



The reliable, powerful and durable forms printer – built for speed and performance.

Designed for high-volume forms printing, standalone or shared by a workgroup, the PACEMARK® 4410 heavy-duty impact printer can tackle your most demanding forms workflow. It simply takes command of the job.

The superb performance of the PACEMARK 4410 is perfectly suited to applications requiring high volume, including long, unattended print runs, general data processing, invoices, billing and financial statements, inventory reports, banking transaction logs, and accounting reports.

Two paper paths (bottom front and rear push) let you load two forms simultaneously: continuous-form stock, including single- and multi-part, card stock, envelopes and labels. And the paths can be selected via the front panel or through the printer software that's included.

Exceptional reliability – The PACEMARK 4410 is rated at 15,000 hours (about 7.25 years of 40-hour work weeks!) or 3,045,000 pages (35,000 pages per month!).

For strength and stability, the PACEMARK 4410 has a larger, beefier carriage assembly, ensuring optimal print quality. The metal chassis gives the printer greater rigidity and strength in rugged environments. Even the tear bar is long-lasting metal, for clean, precise cutting.

Powerful, too – The PACEMARK 4410 prints clearly on the last page of a 10-part form, and handles card stock just as easily. It delivers 300 lines per minute/1,066 characters per second in High-Speed Draft mode—and a 15 ips feed rate.

There's no question about it: if you need reliability, power and endurance in a forms printer, the printer that commands attention is the PACEMARK 4410.

And ensuring that outstanding performance is an industry-leading on-site warranty: 2 years parts and labor.

Expect more from a PACEMARK® 4410 printer: fast speeds... exceptional performance. This is one reliable, powerful and durable forms printer.

Highlights:

- **Designed for high-volume, lengthy, unattended print runs: general data processing, report generation, transaction logs, spreadsheets**
- **15,000-hour/35,000 page-per-month MTBF**
- **300 lines-per-minute print speed (1,066 cps)**
- **Crisp, clear printing – even on 10-part forms**
- **Standalone or network-ready:**
 - Network-ready model pre-configured with 10/100 Base-T Ethernet internal print server
 - Standalone model is networkable via optional Ethernet internal print servers
- **Rugged metal design for stability and years of heavy use**
- **2-Year On-Site limited printer warranty (parts and labor)¹**
- **Live, toll-free technical support¹**

¹ Available in the U.S. and Canada only.



PACEMARK® 4410

Specifications

Technology, Speed and Print Characteristics

- **Print Method:** Serial Impact Dot Matrix (SIDM)
- **Printhead:** User-replaceable 2 x 9-pin diamond array
- **Format:** Wide-carriage (136 column) only
- **Print Speed / Character Matrix:**

Mode	NLQ	Utility	HSD
Speed (in cps)	200	800	1,066
- **Lines per minute:** Up to 300
- **Feed Rate:** 15 inches per second (ips)

Emulation, Interface and Memory

- **Emulations:** Epson® FX, IBM® ProPrinter® III, OKI® MICROLINE® co-resident
- **Interfaces:** Standard on both models – IEEE 1284 bi-directional parallel and RS-232C serial (supports 38.4K data rates); on PM4410n – Ethernet® via OKiLAN® 7130e 10/100 Base-T Internal Print Server¹
Optional on PM4410 – OKiLAN® 7130e 10/100 Base-T Internal Print Server¹
- **Standard Memory:** 512K RAM; Receive buffer 16K, 28K and 56K max. (no DLL)

Compatibility

- **Feed Rate:** 15 inches per second (ips)
- **Operating Systems:** Windows® 10, Windows 8.1, Windows 8, Windows 7, Server 2019, Server 2016, Server 2012/R2, Server 2008/R2, 2000

Note: Check website for most current OS compatibility.

Fonts/Characters

- **NLQ:** Courier, Gothic
- **Utility/HSD/SSD:** Gothic
- **Scalable (22 – 216 pt.):** Courier, Gothic
- **Code Pages:** Standard ASCII; Epson® Character Set I & II; IBM® Character Set I, II & All; International Character Sets including BRASCI & ABICOMP; Line/Block Graphics; Multilingual 858; ISO 8859/15
- **Bar Codes:** 8

Paper Handling

- **Paper Input:** Continuous: single-part/multi-part; card stock; envelopes; labels
- **Number of Copies:** Interleaf = 7; Carbonless = 10 (Front Bottom Feed)
- **Maximum Thickness:** Rear Feed: 0.014" (0.36 mm) Front Bottom Feed: 0.031" (0.78 mm)
- **Paper Feeding:** Rear Push and Front Bottom Push standard
- **Tear Capabilities:** Zero tear (Menu-selectable); Metal tear bar
- **Loading:** Auto loading, Auto paper park, Autogapping, Straight paper path (front), Software-selectable front/rear paper paths
- **Sensors:** Paper out, paper input, Paper motion/Jam detection, Paper width, Paper selected

Warranty and Reliability

- **Warranty:** 2-year On-site limited warranty on printer (parts & labor)²
- **MTBF:** 15,000 hours (25% duty cycle/35% page density)
- **Monthly Workload:** 35,000 pages at 25% duty cycle/35% density
- **Printhead Life:** 400 Million characters avg. in 10 cpi Utility mode (25% duty, 35% page density)
- **Ribbon Life:** 15 million characters

Environmental

- **Size (WxDxH):** 30.2" x 15.2" x 14.1" (76.8 cm x 38.5 cm x 35.8 cm)
Note: Size does not include paper support and rubber foot.
- **Net Weight:** 92.6 lb. (42 kg)
- **Maximum Noise:** 61 dBA (Utility), 55 dBA (Utility-Quiet)

Ordering Information

Description	Part Number
Printers	
PACEMARK 4410 – 110V – 240V	61800901
PACEMARK 4410n – 110V – 240V (factory-configured with OkiLAN® 7130e 10/100 Base-T Ethernet Internal Print Server)	61801001
Ribbons	
Ribbon cartridge – Nylon fabric (15 Million character life)	40629302
Accessories	
PM4410 Network Adapter 10/100 Base-T Kit	70050001
OkiLAN® 7130e 10/100 Base-T Ethernet Internal Print eServer	45268701
HSP Adapter for Network Version	41139809
OKIcare® Warranty Enhancement Programs	
OKI Depot™	OKI On-Site™
3-Year Extension	58251711
	58252711

Note: All Warranty Enhancement Program options extend the total warranty coverage period from the date of purchase to the number of years listed for each order number above.

¹ Factory-configured only.

² Available in the U.S. and Canada only.

³ Requires PM4410 Network Adapter Kit

All specifications subject to change without notice.

© 2020 Oki Data Americas, Inc. OKI, MICROLINE, OkiLAN, OKIcare Reg. T.M., Oki Electric Industry Co., Ltd. PACEMARK Reg. T.M., Centronics Reg. T.M., Centronics Data Computer Corp. Epson, Reg. T.M., Seiko Epson Corp. IBM, OS/2, ProPrinter Reg. T.M., International Business Machines Corp. Windows, Windows NT, LAN Manager Reg. T.M., Microsoft Corp. UNIX Reg. T.M., Santa Cruz Operation (SCO). PostNet Reg. T.M., USPS.

Oki Data Americas, Inc.

USA
8505 Freeport Pkwy., Suite 600
Irving, TX 75063
Tel: 800.OKI.DATA (800.654.3282)
Fax: 856.222.5320

www.oki.com/us

Canada
5800 Hurontario St., Suite 1020
Mississauga, Ontario L5R 4B9
Tel: 905.755.5800
Fax: 905.755.5840

www.oki.com/ca

