

Product data sheet

Specifications



Rack PDU, Basic, 1U, 16A, 208&230V, (10)C13 & (2)C19



AP9559

Overview

Lead time Usually in Stock

Main

Color	Black
Product or Component Type	PDU
PDU Type	Basic
Cord length	8.2 ft (2.5 m)
Number of cables	1
Provided Equipment	User Manual Rack Mounting brackets

Complementary

Input Voltage	120 V 208 V 230 V
Height	1.7 in (4.4 cm)
Width	17.6 in (44.7 cm)
Output Voltage	120 V 208 V 230 V
Depth	2.2 in (5.7 cm)
Net Weight	2.16 lb(US) (0.98 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Input Plug Type	IEC 60320 C20
Mounting Mode	Rack-mounted
Rack units	1U
Mounting position	Horizontal
Acceptable Input Voltage	90...250 V
Max line current	16 A
Input current limits	16 A
Load Capacity	3680 VA
Input Frequency	50/60 Hz

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Outlet type and quantity	10 IEC 60320 C13 2 IEC 60320 C19
---------------------------------	-------------------------------------

Environment

Product Certifications	cUL Listed CE UL Listed VDE Victoria
-------------------------------	--

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
--	-------------------------

Relative Humidity	0...95 %
--------------------------	----------

Operating altitude	0...10000 ft
---------------------------	--------------

Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
--	----------------------------

Storage Relative Humidity	0...95 %
----------------------------------	----------

Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)
-------------------------	--

Ordering and shipping details

GTIN	731304123521
-------------	--------------

Packing Units

Unit Type of Package 1	PCE
-------------------------------	-----

Number of Units in Package 1	1
-------------------------------------	---

Package 1 Height	6.5 in (16.5 cm)
-------------------------	------------------

Package 1 Width	19.02 in (48.3 cm)
------------------------	--------------------

Package 1 Length	6.0 in (15.2 cm)
-------------------------	------------------

Package 1 Weight	5.192 lb(US) (2.355 kg)
-------------------------	-------------------------

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

 Energy Efficient Product

 Take-Back Program Available

Well-being performance

 Lead Free

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Circularity Profile

[End of Life Information](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov