

Affordable All-in-One with camera direct printing.  
Quality prints, copies and scans.



### Key Selling Features

- 2 picolitre FINE print-head technology results in sharper text and enhanced image detail
- Produce high-quality photos and documents at up to 4800 x 1200 dpi<sup>1</sup>
- Features "Dual Gamut Colour Processing Technology" for optimised copies and photo reprints
- Create true borderless 6" x 4", 5" x 7" and A4 size photos
- Print a borderless 6" x 4" photo in around 52 seconds<sup>2</sup>
- Print and copy at up to 22 ppm black and 17 ppm colour<sup>2</sup>
- PictBridge compatible for digital camera printing – no computer required<sup>3</sup>
- Scan high-quality photos and documents at up to 600 x 1200 dpi
- USB 2.0 Hi-Speed interface ensures fast data transfer<sup>4</sup>

### Short Description

The MP160 allows you to produce quality prints, copies and scans at home. Print your photos directly from compatible digital cameras with no need for a computer. The MP160 can scan at up to 600 x 1200 dpi and copy your documents as fast as 22 ppm black and 17 ppm colour. Together with high print resolution of up to 4800 x 1200 dpi, fast 6" x 4" photo print speed of approximately 52 seconds and borderless photo prints up to A4 size, the PIXMA MP160 is the perfect All-in-One for students or the whole family.

### ChromaLife100

A beautiful photograph is something worth keeping forever. Now with ChromaLife100, the photos you print at home can maintain all their vibrancy and colour for 100 years<sup>5</sup>. The combination of genuine Canon ChromaLife100 ink and selected Canon photo papers lets you print long-lasting photos of unrivalled quality. Thanks to ChromaLife100, the precious memories in your albums will still be bright and fresh a century from now. Canon has a range of specialty photo papers that's suitable for virtually every photo size and use. To ensure you gain all the long-lasting benefits of ChromaLife100, make sure you choose Canon's Photo Paper Pro, Photo Paper Plus Glossy, Photo Paper Plus Semi-gloss or Glossy Photo Paper.

### As A Printer

- 2 picolitre FINE (Full-photolithography Inkjet Nozzle Engineering) print-head technology and 4800 x 1200 dpi for high quality photos and documents<sup>1</sup>
- Borderless photo printing on 6" x 4", 5" x 7" and A4 paper
- Prints a borderless 6" x 4" photo in around 52 seconds<sup>2</sup>
- Fast document printing up to 22 ppm in black and 17 ppm in colour<sup>2</sup>
- Print photos directly from compatible digital cameras using PictBridge technology<sup>3</sup>

### As A Copier

- Copy up to 22 cpm black and 17 cpm colour<sup>2</sup>
- Produce multiple copies up to 9 pages

### As A Scanner

- Scan high-quality photos and documents at up to 600 x 1200 dpi
- 48-bit input / 24-bit output colour depth
- Advanced Z-Lid for copying and scanning thick items such as books or magazines

# PIXMA MP160 Specifications

## Printer Functions

### Printing Speed<sup>2</sup>

Monochrome: approx. 22 ppm, Colour graphics: approx. 17 ppm

Photo Paper Plus Glossy (6" x 4" image on PP-101 in standard mode): approx. 52 secs borderless

### Printing Resolution<sup>1</sup>

4800 x 1200 dpi

### Borderless Printing

A4, 5" x 7", 6" x 4", Credit Card (54mm x 86mm)

### Ink Cartridges

CL-41 – FINE Colour Cartridge (or optional High Yield CL-51 Cartridge)

PG-40 – FINE Black Cartridge (or optional High Yield PG-50 Cartridge)

### Ink Yield\*

CL-41 – 120 borderless 6" x 4" photos, CL-51 – 198 borderless 6" x 4" photos

### Paper Type & Capacity

Plain Paper (10mm): 100 sheets

Super White Paper (SW-201): A4: 100 sheets

High Resolution Paper (HR-101N): A4: 80 sheets

Photo Paper Pro (PR-101): A4: 10 sheets, 6" x 4": 20 sheets

Photo Paper Plus Glossy (PP-101): A4/5" x 7": 10, sheets, 6" x 4": 20 sheets

Photo Paper Plus Semi-gloss (SG-101): A4: 10 sheets, 6" x 4": 20 sheets

Glossy Photo Paper (GP-401): A4: 10 sheets, 6" x 4"/Credit Card: 20 sheets

Glossy Photo Paper (everyday use) (GP-501): A4:10 sheets, 6" x 4": 20 sheets

Matte Photo Paper (MP-101): A4:10 sheets, 6" x 4": 20 sheets

Photo Paper Plus Double Sided (PP-101D): A4/5" x 7": 1 sheet manual feed (not supported for Mac OSX)

Photo Stickers (PS-101): 1 sheet

T-Shirt Transfer (TR-301): A4: 1 sheet

Envelope (DL, COM#10): 10

### Supported Paper Sizes

A4, Letter, Legal, A5, B5, Envelopes(DL, COM10), 4"x6", 4"x8", 5"x7", 8"x10", Credit Card (54mm x 86mm)

### Supported Paper Weights

Plain Paper: 64-105g/m<sup>2</sup>. Canon specialty paper (max paper weight): approx 273g/m<sup>2</sup> (Photo Paper Plus Double Sided)

## Copier Functions

### Colour Copy

Yes

### Image Quality

Fix (only plain paper: Fast, Standard)

### Copy Speed<sup>2</sup>

Mono: Up to 22 cpm, Colour: Up to 17 cpm

### Multiple Copy

up to 9 copies

### Other Copy Functions

Fit-to-page

## Scanner Functions

### Scanner Type

Flatbed scanner by CIS

### Scanner Resolution

600 x 1200 dpi (19200 x 19200 optimised)

### Colour Scanning Depth

48 bit input and 24 bit output

### Other features

Advanced Z-Lid (up to 20mm), Push Scan (only starting ScanGear), Image Corrections

### General Features

### Interface Type

PC: USB 2.0 Hi-Speed<sup>4</sup>

Camera Direct: Direct Print Port (PictBridge)<sup>3</sup>

Windows 98/2000/Me/XP and Mac OS.X (10.2.8 or later)

### Supported OS

Easy-PhotoPrint, Easy-WebPrint<sup>5</sup>, MP Navigator, ArcSoft<sup>®</sup> PhotoStudio<sup>®</sup> and ScanSoft<sup>®</sup> OmniPage<sup>®</sup> SE (Win 98 not supported)

### Weight

Approx. 6.3kg

### Power Source

AC 100-240V, 50/60Hz

### Power Consumption

Max: 13W (copying), Standby: 2W

### Dimensions (W x D x H)

443 x 381 x 181 mm

### Included As Standard

PIXMA MP160 All-in-One printer, Setup Software & User's Guide CD-ROM, PG-40 FINE black cartridge, CL-41 FINE colour cartridge, 12 months warranty card, Power cord

\* Ink yield calculation is based on printing Canon 24 standard digital images on Photo Paper Plus Glossy (6" x 4" borderless print) with default settings in Windows XP driver. The figure above is an average value, measured when printing continuously using the ink immediately after it is unsealed, until the ink is out. Ink yield may vary depending on photos printed, applications software used, print mode and type of paper used. This should be used as a guide only and does not take into account ink that might be used for head cleaning or head refreshing to maintain printer performance. Please visit our website for further details.

1. Ink droplets can be placed with a horizontal pitch of 1/4800 inch at minimum.
2. Print and copy speed dependent on system configuration, image/document complexity, type of paper used, software, print mode and does not take into account data processing time on host computer.
3. PictBridge camera direct printing requires PictBridge compatible digital cameras in order to function. Check with your digital camera manufacturer or users guide to determine PictBridge compatibility.
4. USB 2.0 Hi-Speed performance requires Windows XP with Service Pack 1 or Windows 2000 with Service Pack 4 with pre-installed USB 2.0 Hi-Speed port.
5. Up to 100 Years' Life in a Photo Album when printed with ChromaLife100 ink on selected Canon photo papers. Kept in a photo album, shut out light and air (gas), temperature 23 degrees and 50% humidity. Predicted value from the accelerated test. Result may vary based on individual environmental factors. For more information, please visit [canon.com.au/ChromaLife100](http://canon.com.au/ChromaLife100)
6. Easy-WebPrint requires Microsoft<sup>®</sup> Internet Explorer version 5.5, version 6.0 recommended.

All specifications may change without notice.