

HP LaserJet M5025 MFP



Fulfill your 11 by 17 printing and copying needs and enjoy send-to-e-mail and optional fax functionality¹ with the new HP LaserJet M5025 MFP—an affordable MFP that makes processes simple and efficient.

Boost performance

- **Get more work done.** This device sets the pace for success with print and copy speeds up to 25 ppm. Instant-on Technology reduces warm-up time from minutes to seconds, so you see a fast first page.
- **Provide big impact in a small size.** The MFP offers the 11 by 17 printing you want, and its smaller footprint enables placement close to workgroups, where you need it.
- **Scan and send your documents via e-mail.** Get the digital sending features most suited to your office needs with convenient send-to-e-mail and simple address storage.²
- **Support efficiency with more input capacity.** The last thing you want to do is reload the MFP when you're pressed for time. That's why the input capacity of up to 2,100 sheets—600-sheet standard capacity plus other optional configurations—is a welcome relief.³ An ADF accommodates 50 sheets of letter-, legal-, and 11 by 17-sized paper.

Easy to use, easy to succeed

- **Work without interruption.** Designed to minimize interruptions, interactive HP Smart printing technology in the HP LaserJet print cartridge and the MFP optimizes print quality, provides convenient troubleshooting, enables status monitoring, sends alerts when supplies are low, and facilitates convenient on-line supplies reordering.⁴

- **Save time and ensure privacy with an embedded hard disk.** Stop running back and forth. Proof one copy at the MFP before releasing the rest from the MFP's control panel. Need privacy? Print sensitive material to a virtual mailbox with password protection. Enjoy high-capacity storage of documents that you frequently use, such as expense reports or invoices.

World-renowned quality

- **Need consistent results and worry-free printing?** The HP LaserJet print cartridge and HP toner formula are specifically designed to achieve professional quality with crisp, sharp text and lines every time you print. Comprising up to 70 percent of the device's printing system, you refresh your MFP with every original HP LaserJet print cartridge, ensuring reliable, precise results.
- **Experience smooth operation.** Complex jobs are not a problem. A 460 MHz processor and 256 MB of memory enable the device to process jobs easily and quickly. You also experience a quick return to the print job's application for increased uptime.

HP printing and imaging systems help you create powerful, professional communications easily. HP multifunction products, supplies, accessories, and services are designed to work together and are invented to meet your business needs.

¹Fax functionality is an optional feature that can be added to the HP LaserJet M5025 MFP (not included, sold separately).


²Digital sending features are not upgradeable for the HP LaserJet M5025 MFP.

³In addition to a standard input capacity of 600 sheets, optional input is available in two configurations (not included, sold separately): a 500-sheet input tray with cabinet or an integrated 3 by 500-sheet input tray.

⁴Using genuine HP supplies ensures availability of all HP printing features. See your user manual or product Web page for more information on the tools that enable easy printer maintenance and consolidated supplies reordering. For more information, visit www.hp.com/learn/suresupply.

HP LaserJet M5025 MFP

- 1 50-sheet automatic document feeder (ADF) automatically scans two-sided documents in full color
- 2 Color flatbed scanner
- 3 New control panel design features a touch-screen graphical display
- 4 250-sheet output bin
- 5 Two 250-sheet input trays
- 6 Upper-right access door to the print cartridge
- 7 100-sheet multipurpose tray 1
- 8 Right side access door
- 9 USB accessory connection
- 10 A powerful 460 MHz processor and 256 MB of standard memory (expandable up to 512 MB)
- 11 One open EIO slot
- 12 Hi-Speed USB 2.0 port
- 13 Security lock slot
- 14 Foreign interface harness (FIH) port
- 15 HP Jetdirect Fast Ethernet embedded print server (RJ-45 port)
- 16 V.34 fax modem port for optional analog fax accessory



Build the wide-format MFP to suit your business



Input trays

Add input capacity with a 500-sheet tray with storage cabinet or integrated 3 by 500-sheet trays



Optional automatic two-sided printing unit

Save time and conserve paper resources with the automatic two-sided printing unit.



Optional analog fax accessory

Add fax capabilities for a complete office hard-copy solution.



Enhanced input/output options

Add wireless, Gigabit Ethernet, or IPsec compatibility via the open EIO slot.



Additional memory

Get up to 512 MB RAM via one open DIMM slot.

Simplicity, convenience, and outstanding support make the HP LaserJet M5025 MFP the perfect choice for small workteams who have no time to worry about device management.



Radically simple

HP completely redefines the term usability with its new, radically simple user interface.

- Easily take advantage of your MFP's complete feature set with an intuitive control panel that clearly displays all available applications. Getting around is a snap with familiar Windows emulation icons, automatic navigation that visually walks you through troubleshooting, and installation wizards that assist with setup.
- The control panel's unique touch-screen graphical display offers all the features you expect from a standard photocopier (as well as optional faxing, scanning, digital sending to e-mail, and printing).
- A built-in Help system explains how to use each screen: just touch the Help button (?) in the upper-right corner of the screen. You can search for specific topics and view explanations of the settings available for an individual job.
- Just like your coffee maker, the Automatic Printer Wakeup feature allows you to set your MFP to be warmed up and ready first thing in the morning.

Legendary HP support

HP's award-winning customer service and support backs every MFP with a one-year limited warranty; fast, knowledgeable online support available 24/7 at www.hp.com/support, and easy-to-access phone support provided by HP trained agents. Plus, you can enhance your warranty protection with the purchase of affordable HP Care Pack Services.

Saves valuable time

The MFP features best-in-class, IPv6-ready networking and management tools via the HP Jetdirect Fast Ethernet embedded print server. Powerful management tools save you time and effort:⁵

- **HP Web Jetadmin** is a simple, Web-based peripheral management utility for remotely installing, configuring, and managing a wide variety of HP and non-HP network peripherals. Through a standard Web browser, you can manage supplies, configure devices, conduct remote diagnostics, set up automatic e-mail alerts, and solve potential problems before they impact user productivity.
- **The HP Embedded Web Server** provides a universal interface to the device that anyone with a network-connected PC and a standard Web browser can easily access. It requires no special software to install or configure. The HP Embedded Web Server allows you to check status information, change settings, and facilitates convenient supplies reordering.
- **The HP Universal Print Driver Series for Windows** can alleviate headaches with a single, intelligent driver that replaces individual drivers for all HP networked devices.⁶ For more information, go to www.hp.com/go/universalprintdriver.

100 million HP LaserJet printers shipped

No one has supplied more printers to more people than HP. For more than 20 years, HP has introduced innovative laser printing products. And now, HP celebrates shipment of the 100 millionth HP LaserJet printer. HP printers offer proven reliability, award winning service and support, and the broadest portfolio of printing solutions in the industry. Count on the legendary quality of HP LaserJet printers.

⁵ IPv6 is only supported with Microsoft Server 2003 and Windows XP (print only).

⁶ The HP Universal Print Driver comes on a CD with the MFP.

HP LaserJet M5025 MFP

Technical specifications

Print and copy speed ⁷	Up to 25 ppm, letter
First page out	Less than 10 seconds
Print resolution	HP FastRes 1200, HP ProRes 1200 (1200 by 1200 dpi), RET (Resolution Enhancement technology)
Features	
Copying	Up to 1,000 multiple copies, optional two-sided copying, reduce/enlarge from 25 to 400% (from scanner glass), contrast (lighter/darker), mixed originals (letter and legal), image adjustment, paper selection, content orientation, pages per sheet, booklet format, optimize text/picture, job build, edge to edge
Scanning	Color flatbed scanner or ADF; scan input modes: front-panel scan, copy, e-mail; file types: PDF, JPG, TIFF, MTIFF
Faxing	Optional accessory
Digital sending	Send-to-e-mail file formats: PDF, JPG, TIFF, MTIFF
Processor	460 MHz
Memory/storage	256 MB RAM (fixed), expandable up to 512 MB via a single open 100-pin DDR DIMM slot; Memory Enhancement technology (MET); 40 GB hard drive
Durability rating	Recommended monthly page volume: ⁸ 3,000 to 12,500 pages Duty cycle: ⁹ up to 200,000 pages per month
Paper	
Handling	100-sheet multipurpose tray 1, 250-sheet input trays 2 and 3, 50-sheet two-sided reversing automatic document feeder
Output	250-sheet output bin
Two-sided printing	Optional automatic two-sided printing accessory
Sizes	100-sheet multipurpose tray 1: 3 by 5 in to 12.28 by 18.5 in (76 by 127 mm to 312 by 470 mm) 250-sheet tray 2: 5.83 by 8.27 in to 11.7 by 14.33 in (148 by 210 mm to 297 by 364 mm) 250-sheet tray 3: 5.83 by 8.27 in to 11.7 by 17 in (148 by 210 mm to 297 by 432 mm) Automatic document feeder: 5.43 by 8.27 in to 11 by 17 in (138 by 210 mm to 297 by 432 mm) Flatbed scanner: 8.5 by 11 in to 11.7 by 17 in (215.9 by 279.4 mm to 297 by 432 mm)
Weights	Input trays: 16 to 32 lb (60 to 120 g/m ²) Automatic document feeder: 16 to 28 lb (60 to 105 g/m ²)
Types	Paper (plain, printed, letterhead, prepunched, bond, recycled, color, rough), transparencies, labels, envelopes, card stock
Connectivity	
Interfaces	One HP Jetdirect Fast Ethernet embedded print server, one Foreign Interface Harness (FIH), one USB type A port, one USB type B port, one open EIO slot, optional analog fax accessory
Languages and fonts	HP PCL6, HP PCL5, HP Postscript level 3 emulation, PDF 1.4; 80 Scalable TrueType fonts
Operating systems	Microsoft® Windows 2000, Windows Server 2003 x86, XP x86, Windows Server 2003 x64, XP x64; compatible with the Windows Vista™ operating system at Windows Vista release; Mac OS X v10.2.8, v10.3, v10.4 or later, PowerPC G3, G4, G5, and Intel Core processor
Network operating systems	Via HP Jetdirect print servers: Windows 2000, XP Home, XP Professional, XP Professional x64, Server 2003; Novell 5.1 and higher; Mac OS X v10.2.8, v10.3, v10.4 and higher; Red Hat Linux 7.x and higher; SuSE Linux 8.x and higher; HP-UX 10.20, 11.x, 11.i; Solaris 2.5 and higher (SPARC systems only); IBM AIX 3.2.5 and higher (requires software from NOS vendor); MPE-iX; Citrix MetaFrame Server; Windows Terminal Services
Network protocols	IPv6, ¹⁰ DHCPv6, HTTP, HTTPS, Port 9100, LPD, IPP, Secure IPP, MLDv6, ICMPv6; IPv4: FTP, IPP, Secure IPP, Auto-IP, Apple Bonjour Compatible, Telnet, SLP, IGMPv2, BOOTP/DHCP, WINS, SNMPv1/v2c/v3, TFTP, HTTP, HTTPS, Port 9100, LPD; Other: IPX/SPX, DLC, LLC, Apple
Security	Private print, HP Secure Storage Erase, HP JetDirect — 802.1x for wired networks, SNMPv3 and HTTPS, and Secure IPP (IPP-S) and IPsec
Dimensions (W by D by H)	24 by 22.5 by 23 in (610 by 571 by 584 mm)
Weight	121 lb (55 kg)
What's in the box	HP LaserJet M5025 MFP, power cord, original HP LaserJet print cartridge, control panel overlay, Getting Started Guide, Wall Poster, software/documentation CD

Recommended temperature	63 to 77 degrees F (17 to 25 degrees C)
Storage temperature	50 to 99 degrees F (13 to 38 degrees C)
Recommended humidity	30 to 70 percent, non-condensing
Sound power ¹¹	Active: 6.6 B(A) printing; 7.1 B(A) copying
Bystander sound pressure ¹¹	Active: 51 dB(A) printing; 56 dB(A) copying
Power specifications	110-volt models: 115 to 127 V (± 10 percent), 60 Hz (± 2 Hz); 12 amp 220-volt models: 220 to 240 V (± 10 percent), 50 Hz (± 2 Hz); 6 amp
Power consumption ¹²	Active: 600 watts; Active copy: 1265 watts; Ready: 28 watts; Sleep: 24 watts; Off: 0.1 watt Typical Electricity Consumption (TEC): 5.628 kWh/Week ENERGY STAR® qualified models; see http://www.hp.com/go/energystar
Safety certifications	Canada (cUL-CAN/CSA C22.2 No.60950-1-03), USA (UL-UL 60950-1; FDA-21 CFR Chapter 1 Subchapter J for lasers), Class 1 Laser/LED Product
EMC certifications	CISPR 22:1993/EN 55022:1994 Class A, EN 61000-3-2:2000, EN 61000-3-3:1995, EN 55024:1998, FCC Title 47 CFR, Part 15 Class B/ICES-003, Issue 4/G9B254-1998, GB17625.1-2003, EMC Directive 89/336/EEC and the Low Voltage Directive 73/23/EEC, and carries the CE-Marking accordingly
Telecom	TBR-21:1998; EG 201 121:1998, FCC Part 68, Industry Canada CS03, NOM-151-SCTI-1999 (Mexico)
Warranty	One year, next business day, onsite warranty with free phone support during warranty
HP SureSupply enabled	To learn more, please visit www.hp.com/go/SureSupply

⁷ Print speed may slow down on large jobs using letter/landscape and ledger sized paper. The degree of speed reduction will depend upon paper weight and fuser mode, and is determined by the maximum allowable fuser temperature. Copy speed specifications are based on long-edge feed (landscape) scanning through the ADF.

⁸ HP recommends that the number of pages per month of imaged output be within the stated range for optimum device performance, based on factors including supplies replacement intervals and device life over an extended warranty period.

⁹ Duty cycle is defined as the maximum number of pages per month of imaged output. This value provides a comparison of product robustness in relation to other HP LaserJet or HP Color LaserJet devices, and enables appropriate deployment of printers and MFPs to satisfy the demands of connected individuals or groups.

¹⁰ IPv6 is only supported with Microsoft Server 2003 and Windows XP (print only).

¹¹ Configuration tested: base model, simplex printing, A4 paper at an average of 25 ppm. Based on copying with ADF running.

¹² Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty.



© Copyright 2006-2007 Hewlett-Packard Development Company, L.P.

The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein. ENERGY STAR and the ENERGY STAR logo are registered U.S. marks. Microsoft, Windows, and Windows XP are U.S. registered trademarks of Microsoft Corporation. Windows Vista is a trademark or registered trademark of Microsoft Corporation in the United States and/or other countries.

Printed in the U.S.A.

For more information visit our website at www.hp.com

4AA0-6844ENUC, 07/2007, Rev. 4.3

Ordering information

Product	Number
HP LaserJet M5025 MFP	Q7840A
Supplies	
HP LaserJet Black Print Cartridge with Smart Printing Technology.	Q7570A
Average cartridge yield 15,000 standard pages ¹³	
HP Printer Maintenance Kit 110V	Q7832A
ADF Maintenance Kit	Q7842A
Connectivity	
HP Jetdirect en1700 USB 2.0 Print Server ¹⁴	J7988G
HP Jetdirect en3700 USB 2.0 Print Server ¹⁵	J7942G
HP Jetdirect ew2400 wireless USB 2.0 Print Server ¹⁵	J7951G
HP Jetdirect 175x Fast Ethernet USB external Print Server ¹⁵	J6035G
HP Jetdirect 630n IPv6 Gigabit Ethernet Print Server	J7997G
HP Jetdirect 635n IPv6/Psec internal Print Server	J7961G
Accessories	
Automatic two-sided printing accessory	Q7549A
Analog fax accessory	Q3701A
500-sheet input tray 4 with storage cabinet	Q7834A
Integrated 3 by 500-sheet input trays 4, 5, and 6	Q7835A
Memory and storage	
128 MB 100-Pin DDR DIMM	Q7718A
256 MB 100-Pin DDR DIMM	Q7719A
HP EIO Serial ATA High Performance Hard Disk	J7989G
Cables	
USB, 2-meter A to B cable	C6518A
Service and support	
3-year, next business day, HW support	UE719E
4-year, next business day, HW support	UE720E
5-year, next business day, HW support	UE721E
3-year, 4-hour response, 9X5 HW support	UE996E
4-year, 4-hour response, 9X5 HW support	UE997E
5-year, 4-hour response, 9X5 HW support	UE998E
3-year, 4-hour response, 13X5 HW support	UE999E
4-year, 4-hour response, 13X5 HW support	UFO00E
5-year, 4-hour response, 13X5 HW support	UFO01E
1-year, post-warranty, next business day, HW support	UFO02PE
1-year, post-warranty, 4-hour response, 9X5 HW support	UFO03PE
1-year, post-warranty, 4-hour response, 13X5 HW support	UFO04PE
Network installation: high-end HP LaserJet MFP service	U2014E

Paper
North America: www.hp.com/go/paper USA: 1-800-477-5010

¹³ Declared yield value in accordance with ISO/IEC 19752. For more information, visit www.hp.com/go/pageyield.

¹⁴ Supports printing only, no software scan, no webscan.

¹⁵ Supports printing only, no webscan.

