

6 ft USB to Parallel Printer Adapter - M/M

StarTech ID: ICUSB1284



The ICUSB1284 6 ft USB to Parallel Printer Adapter - M/M allows USB capable PCs to print to any standard parallel printer, converting a USB port into a Centronics (male) connector for direct connection to a parallel printer.

The USB interface provides a much faster data transfer rate than standard parallel ports, thereby reducing the time spent waiting for a print job or data transfer to be sent.

A portable, space-saving solution, the USB to Parallel Printer Adapter is self-powered and provides Plug and Play installation on Windows® based, USB-compliant computers.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Allows you to quickly add a parallel port to your Windows® computer

Features

- High speed bi-directional parallel port compliant to IEEE-1284 industry standard
- Low power consumption as it draws power from the USB connection
- Fully Plug & Play for easy installation
- No IRQ required for installation

Technical Specifications

Warranty	2 Years
Ports	1
Interface	Parallel
Bus Type	USB 2.0
Chipset ID	Prolific - PL-2305
Connector Type(s)	1 - Centronics (36 pin) Male
Connector Type(s)	1 - USB A (4 pin) Male
OS Compatibility	Windows® 8 / 8.1 (32/64bit), 7 (32/64), Vista (32/64), XP (32/64), 2000, ME, 98SE Windows Server® 2012, 2008 R2, 2003, 2000 Mac OS® 10.x (Tested up to 10.10) Linux 2.6.x – 3.9.x
Enclosure Type	Plastic
Cable Length	5.9 ft [1.8 m]
Product Length	6.1 ft [1.9 m]
Product Weight	3.9 oz [110 g]
Power Source	USB-Powered
Power Consumption	0.9W
Operating Temperature	5°C to 40°C (41°F to 140°F)
Storage Temperature	-20°C to 70°C (-4°F to 158°F)
Humidity	0~80% RH non-condensing
Shipping (Package) Weight	0.3 lb [0.2 kg]
Included in Package	1 - USB to Parallel Converter Cable
Included in Package	1 - Driver CD

Certifications, Reports and Compatibility

