

15 ft DVI-I Dual Link Digital Analog Monitor Cable M/M

StarTech ID: *DVIIDMM15*



The DVIIDMM15 15ft DV-I Dual Link cable features 2 male DV-I (29-pin) connectors and provides a reliable connection between your desktop or laptop computer and a DV-I monitor or projector.

The 15ft DV-I male to male cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

Applications

- Connect your desktop or laptop computer to a DV-I Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards
- Supports both analog and digital displays

Technical Specifications

Warranty	Lifetime
Industry Standards	DVI DDWG Standard
Connector A	1 - DVI-I (29 pin) Male
Connector B	1 - DVI-I (29 pin) Male
Maximum Data Transfer Rate	9.9 Gbits/sec
Color	Black
Wire Gauge	28 AWG
Cable Length	15 ft [4.6 m]
Shipping (Package) Weight	1 lb [0.5 kg]
Included in Package	15 ft DVI-I Dual Link Digital Analog Monitor Cable M/M

Certifications, Reports and Compatibility

