

2 Port Professional USB KVM Switch Kit with Cables

StarTech ID: SV231USBGB



The SV231SUBGB 2 Port Professional USB KVM Switch Kit with Cables offers simple control of 2 computers from a single monitor/display and USB peripheral set (keyboard, mouse).

The 2 Port KVM includes 2 USB KVM cables, for a complete out-of-the-box solution saving you time and money. An integrated 3 port USB hub allows you to share USB peripherals between computers as though they were connected directly. A compact form factor and rear-port connections minimizes disruption to your workspace.

This OS independent KVM supports resolutions up to 1920x1440, and provides a smooth operating experience in mixed (Windows/Mac/Linux) environments.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Applications

- Dual system control for a single workstations increasing user productivity in the office
- Provide centralized control for multiple high-res Digital Signage server control
- Great for manufacturing line computer control, simplifying access to multiple systems
- Perfect for PC test/burn-in computer control saving the desk space required for two monitors, keyboards and mice

Features

- Control 2 computers from one USB keyboard/mouse/monitor
- Share 3 different USB peripherals using the integrated hub
- High 1920x1440 resolution capability
- Front panel push buttons for easy computer selection
- OS independent - No software or drivers required
- Supports keyboard and mouse plug and play
- Selectable auto scan time interval
- Supports DDC2B VGA monitors
- Universal Power Adapter with EU and UK prong types included

Technical Specifications

Warranty	3 Years
Audio	No
KVM Ports	2
PC Interface	USB
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	No
Cables Included	Yes
U Height	1U
Daisy-Chain	No
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	3 - USB A (4 pin) Female
Host Connectors	2 - USB B (4 pin) Female
Host Connectors	2 - VGA (15 pin; High Density D-Sub) Male
DVI Support	No
IP Control	No
Maximum Cable Length	5 m [16.4 ft]
Maximum Analog Resolutions	1920x1440
Auto Scan	3, 8, 15 & 30 seconds
Maximum Number of Users	1
Port Selection Support	Push Button
Color	Black
Enclosure Type	Steel
Product Width	124 mm [4.9 in]
Product Height	40 mm [1.6 in]
Product Depth	70 mm [2.8 in]
Product Weight	420 g [14.8 oz]
Power Adapter Included	Yes
Input Voltage	110 ~ 240 AC
Input Current	0.4A
Output Voltage	5 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	M

Shipping (Package) Weight	1505.95
Included in Package	1 - 2 Port KVM Switch
Included in Package	2 - 6ft(1.83m) KVM Cables
Included in Package	1 - Universal power adapter (EU/UK)
Included in Package	1 - User Manual

Certifications, Reports and Compatibility

