

# Assign me

I'm a high performance, hard-working,  
versatile professional.

Lexmark **X2550**

- Up to 22 ppm black and 16 ppm color printing
- 1-touch copy and scan
- Borderless prints up to 5x7"
- Create brilliant photos with optional 6-color printing



SCAN



COPY



PRINT




Put Lexmark to work for you.

**LEXMARK**  
TM

# Lexmark X2550

The Lexmark™ X2550 All-in-One with great speed and performance.

Fast print speeds, versatile functionality and brilliant photo quality in one sleek design.



## General Purpose

### Print

- Fast! Up to 22 ppm black and 16 ppm color printing
- Printing up to 4800x1200 dpi print resolution in photo mode on glossy media

### Copy

- 1-Touch PC-free copying (color or black)
- Reduction/enlargement capacity from 25% - 400%
- 1-99 copies
- One touch borderless copying in popular photo sizes (4x6", 10x15cm)

### Scan

- Flatbed scanner easily handles thick books, reports, and more
- 36-bit color scanner depth; 12-bit grayscale
- Up to 600 x 1200 ppi optical resolution

### Photo

- Fast 4x6", 5x7", L size borderless photos
- Create brilliant photos with optional 6-color printing
- Lexmark Imaging Studio Software makes it easy to crop, rotate and resize photos plus color fix and red eye reduction

### Lexmark Software Suite

- Includes photo editing, copy and scanning software options
- Recore 8 Optical Character Recognition (OCR) software allows you to easily scan hard copy text documents into a soft copy format
- Lexmark Toolbar makes Internet printing easy

### Cartridge Compatibility

- Black: 28(1), 28A, 34 High Yield Color: 29(1), 29A, 35 High Yield Photo: 31



(1) Non-refillable cartridge licensed for single use only. Return empty cartridge only to Lexmark for remanufacturing, refilling or recycling. A variable amount of ink remains when this cartridge must be replaced. Replacement cartridges (28A & 29A) sold without those terms are available through [www.lexmark.com](http://www.lexmark.com). All prices, features, specifications and claims are subject to change without notice.

Lexmark and Lexmark with the diamond design are trademarks of Lexmark International, Inc., registered in the United States and/or other countries. Other trademarks are the property of their respective owners. Microsoft, Windows and the Windows logo are trademarks or registered trademarks of Microsoft Corporation in the United States and/or other countries. The USB-IF logo is a trademark of Universal Serial Bus Implementers Forum, Inc. ENERGY STAR® is a U.S. registered mark. Mac and Macintosh are trademarks of Apple Computer, Inc., registered in the United States and other countries. Microsoft, Windows Vista and the Windows Vista logo are trademarks or registered trademarks of Microsoft Corporation in the United States and/or other countries.

All other trademarks are the property of their respective owners. Information in this document is subject to change without notice.  
© 2007 Lexmark International, Inc. 740 West New Circle Road, Lexington, KY 40550. As of 2/07.

## Technical Specifications

### Operating Systems Supported

- Microsoft Windows 2000, XP, XP Professional x64, Vista
- Apple Mac OS X (10.4.4-10.4.x Intel), OS X (10.3.x-10.4.x Power PC)

### Print Noise Level, Operating

- 50 dBA

### Duty Cycle, Maximum

- 3000 Pages per month

### Product Warranty

- One Year Limited Exchange

### Connectivity

- Standard Ports : USB Compatible with USB 2.0 Specification

### Print (ASF) Paper Input Capacity (Maximum)

- 100 pages 20 lb or 75 gsm bond

### Print (ASF) Paper Output Capacity (Maximum)

- 25 pages 20 lb or 75 gsm bond

### Media Sizes Supported

- 10 Envelope, 7 3/4 Envelope, 9 Envelope, A4, A5, B5 Envelope, C5 Envelope, DL Envelope, 6 3/4 Envelope, A2 Baronial, A6 Card, B5, C6 Envelope, Custom, Hagaki Card, Index Card, Executive, Legal, Letter, 4 x 6", Statement, L, 2L, Chokei 3, Chokei 4, Chokei 40, Kakugata 3, Kakugata 4, Kakugata 5, Kakugata 6, 5 x 7", 13 x 18 cm, 10 x 15 cm, 10 x 20 cm, 4 x 8"

### Borderless Printing Media Sizes

- 4" x 6", Hagaki Card, L, 2L, 5" x 7", 3.5" x 5" or 89 mm x 127 mm, 10 x 15 cm, 13 x 18 cm, 10 x 20 cm, 4" x 8"

### Dimensions

- Size (H x W x D) : 6.9 x 16.9 x 11.5 "
- Size, Trays Extended (H x W x D) : 11.26 x 16.9 x 21.0 "
- Weight : 10.4 lbs.
- Packaged Size (H x W x D) : 14.45 x 19.06 x 9.37 "
- Packaged Weight : 13 lbs.
- Pallet Size (H x W x D) : 49.1 x 48 x 40 "
- Pallet Weight : 430 lbs.
- Pallet Quantity : 30

### Pallet Quantity:

### Additional Information

- Text box included so geographies can add country specific information if needed otherwise they can delete this area.
- Text box included so geographies can add country specific information if needed otherwise they can delete this area.
- Text box included so geographies can add country specific information if needed otherwise they can delete this area.
- Text box included so geographies can add country specific information if needed otherwise they can delete this area.
- Text box included so geographies can add country specific information if needed otherwise they can delete this area.

### Product Delivery Date

April 2007

### Standard Box Contents^

- X2550 All-in-One Printer
- One color cartridge (29) and one black cartridge (28)
- One power supply and line cord
- User's Guide and Setup Sheet
- Windows/Mac Installation CD
- Service and Guarantee Information
- 2 Return program envelopes
- This line can be used for any additional country specific items that may be included

^Some models may include additional promotional items



MAC OS X  
Support