

## Power It! 6-Outlet Safety Power Strip, 9 ft. (2.74 m) Cord & Clip, Hang Holes, Safety Covers, GFCI Plug

MODEL NUMBER: TLM609GF



### Highlights

- 6 outlets (including transformer outlets and 4 safety covers)
- 9-ft. (2.74 m) cord with GFCI plug
- Cord wrap with hang holes
- Rugged metal case

### Package Includes

- TLM609GF Safety Power Strip
- 4 safety covers
- Owner's manual

### Description

This Tripp Lite power strip is designed to safely distribute power to connected equipment in harsh environments. It provides a convenient source for multiple outlets wherever they're needed. 6 outlets distribute AC power to a wide range of power tools, drill presses, air compressors, power sanders and more. Convenient transformer outlets accommodate multiple transformers without blocking other outlets. A 9-ft. (2.74 m) grounded cord with integrated cord clip reaches distant outlets. A GFCI plug protects users from electrical shock in wet or humid environments. A lighted on/off switch provides power control over connected equipment. 4 safety covers shield unused outlets from debris and accidental contact. A rugged metal case stands up to the harshest environments. Built-in cord wrap with hang holes provides convenient cord management. Integrated keyhole slots on bottom panel provide convenient wall/desk mounting. Its bright yellow color alerts you and others that power cords and tools are in use.

### Features

- 6 outlets distribute AC power to a wide range of band saws, drill presses, air compressors, power sanders and more.
- Convenient transformer outlets accommodate multiple transformers without blocking other outlets.
- A 9-ft. (2.74 m) grounded cord with integrated cord clip reaches distant outlets.
- A GFCI plug protects users from electrical shock in wet or humid environments.
- A lighted on/off switch with integrated 15 amp circuit breaker provides power control and overload protection over connected equipment.
- 4 safety covers shield unused outlets from debris and accidental contact.
- A rugged metal case stands up to the harshest environments.
- Built-in cord wrap with hang holes provides convenient cord management.
- Integrated keyhole slots on bottom panel provide convenient wall/desk mounting.
- Its bright yellow color alerts you and others that power cords and tools are in use.
- OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may



cause minor or moderate injury. This Tripp Lite product complies with those guidelines.

## Specifications

OVERVIEW	
UPC Code	037332140142
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V, 15A
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	9
Input Cord Length (m)	2.74
Integrated Cord Clip	Yes
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Overload Protection	GFCI plug
Transformer Accommodation	(4) Yes
Outlet Orientation	Single row
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
PHYSICAL	
Color	Yellow; Black
Antimicrobial Coating	No
Color (AC Line Cord)	Yellow
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	209.55mm



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Material of Construction	Metal
Outlets Measurement (Center to Center)	Distance between standard outlets = 30.40mm; Distance between standard outlets and transformer outlets = 45mm
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	5.08 x 17.78 x 42.42
Shipping Dimensions (hwd / in.)	2.00 x 7.00 x 16.70
Shipping Weight (kg)	1.45
Shipping Weight (lbs.)	3.20
Unit Dimensions (hwd / cm)	40.56 x 7.80 x 4.09
Unit Dimensions (hwd / in.)	15.97 x 3.07 x 1.61
Unit Weight (kg)	1.47
Unit Weight (lbs.)	3.24
<b>STANDARDS &amp; COMPLIANCE</b>	
Approvals	cULus, RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>