

## 1U 17" Rackmount LCD Console - USB + PS/2

StarTech ID: RKCONS1701GB



The RKCONS1701GB 1U 17" Rack Mount LCD Console provides a complete keyboard, video and mouse control point, integrated neatly into only 1U of rack/cabinet space - providing complete KVM control right from a server rack.

Offering a durable, compactable 1U design, when the rack console is not in use it's as simple as folding the display like a laptop computer, and sliding it back into the server rack on the sturdy mounting rails (included). The included key lock provides an added security layer, helping to reduce unauthorized access to connected computers.

Offering consolidated control from a convenient location, the KVM rack console can be connected to virtually any multiport KVM switch, for control of multiple servers/computers, providing a scalable KVM control solution that lets you determine the type of KVM switch to use based on function and budget.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applications

- Centralized control of dozens of PCs and servers if used with optional KVM
- Managing cabinet mounted servers
- Improving the internal space efficiency of existing cabinets

### Features

- Bright Active Matrix TFT Display
- Durable design
- OSD function (On Screen Display) for LCD display
- Security features, including port locking and auto scan
- Supports both USB and PS/2 connected servers or KVMs

## Technical Specifications

Warranty	2 Years
Key Lock	Yes
Audio	No
Display Size	17in
Panel Type	Active Matrix TFT LCD
KVM Ports	1
PC Interface	USB and PS/2
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	Yes
Console Interface(s)	1 - USB A (4 pin) Female
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - PS/2 (6 pin; Mini-DIN) Female
Brightness	250 cd/m <sup>2</sup>
Contrast Ratio	1000:1
Pixel Pitch Support	0.264 x 0.264 mm
Response Time	5ms
Viewing Angle	170° (H), 160° (V)
IP Control	No
Maximum Analog Resolutions	1280X1024
Aspect Ratio	Standard (4:3)
Sync	45~80KHZ
Port Selection Support	Hotkeys and OSD (On Screen Display)
Maximum Mounting Depth	31.5 in [800 mm]
Minimum Mounting Depth	21.7 in [550 mm]
Product Height	1.8 in [45 mm]
Product Length	20.9 in [530 mm]
Product Weight	26.5 lb [12 kg]
Product Width	18.9 in [480.8 mm]
Color	Black
Enclosure Type	Heavy Duty Steel
Power Adapter Included	Yes
Output Voltage	12 DC
Output Current	4A

Center Tip Polarity	Positive
Power Consumption	25W
Operating Temperature	0°C to 50°C (32°F to 122°F)
Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Shipping (Package) Weight	38.1 lb [17.2 kg]
Included in Package	1 - 1U LCD Rack Console Drawer (1)
Included in Package	1 - Mounting Rails - Set (1)
Included in Package	1 - Console Cable Kit (1)
Included in Package	1 - Power Adapter (1)

## Certifications, Reports and Compatibility

