




P10PS-JA-400G

GVision's P10PS is a 10.4" screen display designed specifically for use in rugged and harsh point-of-sale (POS) environments where space is at a premium. The P10PS is an ideal solution for customer facing applications where user input is required or when you need multi-media capabilities. The display can easily be mounted on a wall, base, or articulated arm using the included VESA mounting options.

DIMENSION

Unit: Inch



FEATURES

- 10.4-Inch Screen Size
- 800 x 600 Screen Resolution
- LED Backlight Unit
- Resistive Touch Technology (*Option*)
- Spill & Dust Resistant
- Video Signal: VGA
- Integrated Speakers
- Design to Operate 24 / 7 / 365
- 3-Year Warranty

SPECIFICATIONS

DISPLAY		P10PS-JA-400G
Screen Size	10.4 In	
Resolution	800 x 600	
Backlight	LED	
Aspect Ratio	4 : 3	
Viewing Angle	160° / 150°	
Brightness	230cd/m ²	
Contrast Ratio	500 : 1	
Color Depth	262K	
Response Time	15ms	
Display Area (H x V)	211.2 x 158.4 mm	
INTERFACE		
VGA (15 Pin D-Sub)	1	
Audio	1	
USB Type-A	0	
TOUCH TECHNOLOGY		
Technology	N/A	
Type	N/A	
Support OS	N/A	
AUDIO		
Speaker	1W / Per Channel Driver	
CABINET		
Material	Plastic	
Color	Black	
POWER		
Consumption	< 36W	
Electrical Ratings	DC 12V/3A (AC 100V ~ 240V, 50/60Hz)	
TEMPERATURE		
Operating	32° F ~ 104° F (0° C ~ 40° C)	
Storage	-4° F ~ 140° F (-20° C ~ 60° C)	
Humidity	20% ~ 80%	
DIMENSIONS (WxHxD)		
Inch (in)	10.9 x 9.5 x 1.6	
Millimeter (mm)	278 x 242 x 43	
WEIGHT		
Net Weight	3.6 lbs (1.64kg)	
CERTIFICATION		
Certified	CE / FCC / UL / cUL	
VESA™		
Mount Size (mm)	75 x 75	

Specifications subject to change without any notice