



**TAA**   
COMPLIANT

Shown without Ear Rack




# K15TX-CB-0630

GVision's K15TX is a 15" designed specifically for use in kiosk and manufacturing environments. The K15TX includes several flexible mounting options making it easy to integrate into any enclosure or rack. Its rugged all-metal chassis design is able to withstand any almost any environment.

## DIMENSION

Unit: Inch



## FEATURES

- 15-Inch Screen Size
- High Contrast TFT XGA 1024 x 768 Resolution
- Flexible Mounting Solutions: Front / Rack / VESA Mounting
- 5-Wire Resistive Touch Technology
- Supporting Input Interface: DVI / VGA
- Built-in Industrial Power Plug
- Rugged All-Metal Enclosed Chassis
- Design to Operate 24 / 7
- TAA Compliant
- 3-Year Warranty

## SPECIFICATIONS

K15TX-CB-0630	
Screen Size	15 In
Resolution	1024 x 768
Backlight	LED
Aspect Ratio	5 : 4
Viewing Angle	160° / 150°
Brightness	350cd/m <sup>2</sup>
Contrast Ratio	800 : 1
Color Depth	16.2 M
Response Time	8ms
Display Area (H x V)	304.1 x 228.1 mm
INTERFACE	
DVI	1
VGA (15 Pin D-Sub)	1
Audio	1
USB	1
TOUCH TECHNOLOGY	
Technology	Resistive
Type	5-Wire
Support OS	Windows / Linux
CABINET	
Material	Metal
Color	Silver
POWER	
Consumption	< 36W
Electrical Ratings	DC 12V / 3A (AC 100V ~ 240V, 50/60Hz)
TEMPERATURE	
Operating	32° F ~ 104° F (0° C ~ 40° C)
Storage	-4° F ~ 140° F (-20° C ~ 60° C)
Humidity	10% ~ 90%
DIMENSIONS (WxHxD)	
Inch (in)	14.4 x 11.4 x 2.3
Millimeter (mm)	366.5 x 290.5 x 60.2
WEIGHT	
Net Weight	12.7 lbs (5.8 kg)
CERTIFICATION	
Certificate	CE / FCC
VESA™	
Mount Size (mm)	75 x 75

Specifications subject to change without any notice