

4 Port Rack Mountable USB KVM Switch with Audio & USB Hub

StarTech ID: SV431USBAEGB



This Rack Mountable USB KVM Switch supports high resolution video applications (up to 1920x1440 pixels supported) and audio switching between connected computers, and provides an integrated USB 2.0 hub that lets the selected computer have access shared high speed USB peripherals.

Providing control of up to four computers from a single USB keyboard and mouse peripheral set, the switch features a sturdy all metal chassis and can be rackmounted in a server rack/cabinet using an optional [Rackmount Bracket kit](#) (SV431RACK) - minimizing clutter and saving space.

Applications

- Control up to four computers, sharing a single keyboard, mouse, monitor and speakers.
- Integrated USB 2.0 hub allows you to share up to three USB peripherals between the four computers.

Features

- Designed for high-resolution applications: up to 1920x1440 pixels supported
- All metal chassis for long-term durability
- Integrated USB 2.0 hub allows you to share up to three high-speed USB devices between computers
- Audio switching with microphone and speaker connectivity
- Auto-scan function automatically selects computer sequentially
- Compatible with all USB supported Operating Systems
- Front panel push button computer selection

Technical Specifications

Warranty	3 Years
Audio	Yes
KVM Ports	4
PC Interface	USB
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	Optional
Cables Included	No
U Height	1U
Daisy-Chain	No
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - 3.5 mm Mini-Jack (3 Position) Female
Console Interface(s)	2 - USB A (4 pin) Female
Host Connectors	4 - USB B (4 pin) Female
Host Connectors	4 - VGA (15 pin; High Density D-Sub) Male
Host Connectors	8 - 3.5 mm Mini-Jack (3 Position) Female
Other Interface(s)	2 - USB A (4 pin) Female
DVI Support	No
IP Control	No
Maximum Analog Resolutions	1920x1440
Maximum Number of Users	1
Port Selection Support	Push Button
Color	Black
Enclosure Type	Steel
Product Length	220 mm [8.7 in]
Product Width	220 mm [8.7 in]
Product Height	44.5 mm [1.8 in]
Product Depth	130 mm [5.1 in]
Product Weight	1031 g [36.4 oz]
Power Adapter Included	Yes
Input Voltage	110 ~ 240 AC
Input Current	0.4A
Output Voltage	5 DC
Output Current	2A

Center Tip Polarity	Positive
Plug Type	M
Shipping (Package) Weight	1660.18
Included in Package	1 - 4 Port USB KVM Switch With Audio
Included in Package	1 - Pack Rubber Feet
Included in Package	1 - Power Adapter
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

