

## Cat5e KVM Console Extender Kit

MODEL NUMBER: **B013-330**



### Features

- Enables you to control a PS/2 or USB computer/KVM switch from a distance of up to 330ft (100m) away.
- Can control the computer or KVM switch via both Local and Remote Consoles.
- The remote connection is made using standard Cat5e cable
- Display mode of 1600 x 1200 @ 60Hz
- Shielded Cat5e cables provide better transmission integrity

## Specifications

OVERVIEW	
UPC Code	037332143419
Technology	PS/2; USB; VGA/SVGA
PRODUCT OVERVIEW	
Product Overview	Cat5e KVM Console Extender Kit
VIDEO	
Max Supported Video Resolution	1600 x 1200 @60Hz
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	NEMA 1-15P North America

### Highlights

- Manage a PS/2 or USB computer/KVM switch from a remote location up to 330ft (100m) away
- Use readily available Cat5e cable for interconnection

### Package Includes

- Transmitter and Receiver Unit (1 each)
- 3-ft. PC/KVM Cable Kit (1)
- Power Adapter (DC9V, 1A) for Receiver Unit (1)
- 4-ft. (1.22 m) USB A-B Cable (1)
- Quick Start Guide



<b>POWER</b>	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1.0A
External Power Supply Output Specs (V / A)	9V / 1.33A
External Power Supply Cord Length (ft.)	5
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 9.5mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	FCC; UL; cUL; TUV; CB
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Red (Power); Green (Link)
<b>PHYSICAL</b>	
Color	Silver
Material of Construction	Steel
Rackmountable	No
Receiver Unit Dimensions (hwd / in.)	1 x 5.2 x 2.6
Receiver Unit Weight (lbs.)	1.3
Shipping Dimensions (hwd / cm)	13.72 x 17.53 x 20.32
Shipping Dimensions (hwd / in.)	5.40 x 6.90 x 8.00
Shipping Weight (kg)	1.18
Shipping Weight (lbs.)	2.60
Transmitter Unit Dimensions (hwd / in.)	1 x 5.2 x 2.6
Transmitter Unit Weight (lbs.)	1.3
Unit Packaging Type	Box
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	0%-90% RH, Non-Condensing
BTUs	11.9 BTU/Hr
Power Consumption (Watts)	3.5
<b>CONNECTIONS</b>	
Ports	1
Side A - Connector 1	(2) HD15 (FEMALE)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Side A - Connector 2	RJ45 (FEMALE)
Side A - Connector 3	USB B (FEMALE)
Side A - Connector 4	(2) MINI DIN-6 (FEMALE)
Side B - Connector 1	HD15 (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Side B - Connector 3	(2) MINI DIN-6 (FEMALE)
Computer Keyboard and Mouse Interface	PS/2; USB
Computer Monitor Interface	VGA
Console Keyboard and Mouse Interface	PS/2
Console Monitor Interface	VGA
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
Recommended Category Cable	Cat5/Cat5e Cables
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>