



FPS-1032 Version: 4

USB Print Server

Product OverviewThe LevelOne FPS-1032 print server is an ideal network printing solution for small offices, home offices, schools and other businesses that require printer sharing over the same network. This print server is equipped with a 10/100Mbps autosensing Ethernet port and a USB 2.0 port that connected to USB printer.

Multi OS and Network Printing Protocol SupportThe FPS-1032 1-port USB print server supports Windows ME/NT/2000/XP/2003/Vista and Win7 operating systems as well as Mac OS 8.1 and higher, UNIX/Linux and Netware (Bindery/NDS). Network Protocol supported includes TCP/IP, IPX, NetBEUI, AppleTalk, LPR and SMB over TCP/IP for flexible use with different network clients connected to the same office network. The FPS-1032 also includes Internet Printing Protocol (IPP) support and Windows Print Monitor Technology to monitor printing jobs received.
Easy Installation WizardThe LevelOne FPS-1032 is easily configurable using a Web Browser or Windows based configuration program included with the CD-ROM. The print server is easily managed through a Web based user interface and the firmware is upgradeable through TFTP, the windows set-up program or the Web based user interface.

Key Features

- USB print server for network print sharing
- USB 2.0 interface
- Simple setup with user-friendly interface
- Support multiple network printing protocols
- Support multiple operating systems

Specifications

System Specifications

Standards & Protocols:

IEEE 802.3, 802.3u Ethernet Standards

Memory:

System Memory: 16-bit DDR2 16 Mbytes

SPI FLASH Memory: 2 Mbytes

Port:

1x 10/100Mbps Auto-sensing RJ-45 port

Button/Knob:

1xButton(Reset/Load Default/Self-test print)

Indicator:

LAN LED

USB LED



Power Input:
5VDC, 1A (Switching)

Power Consumption:
2.5 Walt

Data Rate:
750 KB/sec

Operating Temperature (°C):
Operating Temperature:0°C to 45°C
Storage Temperature:-5°C to 65°C

Operating Humidity (Non-condensing):
Operating Humidity:0% to 70% relative humidity, non-condensing
Storage Humidity: 0% to 80% relative humidity, non-condensing

Features

General:
LPR,RAW TCP,IPP,SMB
AppleTalk
Netware Bindery/NDS
Print Monitor printing

Security:
Web login

Management:
Web,PSAdmin,Telnet

Physical Specifications


Dimensions (W x D x H mm):
64.8 x 73.2 x 28.4

Weight (g):
57.5g

Approval and Compliance

EMI/EMS:
CE, FCC

Diagram



Order Information

FPS-1032

Package Contents

FPS-1032
Power Adapter
Quick Installation Guide
Resource CD (User Manual, Utility, QIG)

No liability or responsibility for any errors or omissions in the content.
Specifications are subject to change without notice.
All mentioned brand names are registered trademarks and property of their owners.
Copyright © Digital Data Communications GmbH, Germany. All Rights Reserved.