

Specifications



Eaton PW101BA1U140

Eaton Basic PDU, 1PH, 1U, NEMA 5-15P input, 9 ft cord, 1.44kW, 12A, 110-125V, 12 Outlets (12) 5-15R

General specifications

PRODUCT NAME	Eaton basic PDU
CATALOG NUMBER	PW101BA1U140
UPC	743172067494
PRODUCT LENGTH/DEPTH	0.0001 in
PRODUCT HEIGHT	0.0001 in
PRODUCT WIDTH	0.0001 in
PRODUCT WEIGHT	0.0001 lb
WARRANTY	3 year
COMPLIANCES	TAA Compliant
CERTIFICATIONS	UL Listed

Product specifications

FORM FACTOR	1U
OUTLET CONTROL	No
PHASE	Single-phase
WATTAGE	1.44 kW max
AMPERAGE RATING	12A
INPUT VOLTAGE	110-125V
INPUT CONNECTION	5-15P
OUTLETS	(12) 5-15R
CORD LENGTH	9 ft
FREQUENCY RATING	50-60 Hz
ETHERNET INTERFACE	No
OPERATING TEMPERATURE	0° to 60°C (32° to 140°F)

Resources

CERTIFICATION REPORTS	Eaton RoHS Declaration of Conformity: ePDU G3 Eaton RoHS declaration of conformity: ePDU G3
DRAWINGS	PW101BA1U140 T982A1-N-SS-009 Technical Drawing
INSTALLATION INSTRUCTIONS	Eaton ePDU G3 troubleshooting guide
MANUALS AND USER GUIDES	Eaton ePDU G3 operations manual Eaton ePDU G3 replace and configure eNMC module Eaton ePDU G3 1U and 2U installation addendum Eaton ePDU G3 installation and connectivity quick start

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

