

2U 19in Steel Vertical Wall Mount Equipment Rack Bracket

StarTech ID: RK219WALLV



The RK219WALLV 2U 19in Steel Vertical Wall Mount Equipment Rack Bracket offers a versatile storage solution allowing rackmount equipment (Network devices, power strips, patch panels) to be mounted vertically (flush with wall) to save space. Alternatively, the 2U bracket can be installed horizontally under a desk, making it easy to access installed equipment directly from your workspace. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Perfect for SoHo (small office, home office) environments, the wallmount bracket features a sturdy steel design constructed to EIA-310 19in rack standards, and offers space-savings for environments lacking the footprint space for a full size server equipment rack. Suitable for mounting on virtually any wall/ceiling surface (e.g. drywall), the bracket mounting holes are positioned at exactly 16in apart, matching standard construction framework.

Backed by a StarTech.com Lifetime Warranty.

Need more storage space? StarTech.com also offers a [3U 19in Wallmount Bracket](#) and a [4U 19in Wallmount Bracket](#).

Applications

- Mount networking and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space
- Ideal for small and medium businesses needing rack solutions

Features

- Constructed to meet EIA-310 19" rack standards
- Made from solid steel for durability
- TAA compliant for GSA Schedule purchases
- Compatible with most 19" rack mountable equipment
- Arrives fully assembled with cage screws and nuts for mounting equipment
- Wall mounting holes are 16" center to center for greater stability, and mounting into standard wall studs
- Equipment can be vertically wall mounted, or horizontally under a desk

Technical Specifications

Warranty	Lifetime
Fan(s)	No
Frame Type	Open Frame
Front Door Type	Open
Industry Standards	EIA RS310-C
Rack Type	2-Post
U Height	2U
Wallmountable	Yes
Weight Capacity	125.3 lb [56.7 kg]
Note	Package includes 1 ½" screws for mounting to wood surfaces, additional hardware will be required for other materials
Color	Black
External Depth	4.1 in [104.5 mm]
External Height	5.9 in [151 mm]
External Width	19.8 in [504 mm]
Internal Width	17.7 in [450 mm]
Product Weight	28.2 oz [800 g]
Flat Pack	No
Shipping (Package) Weight	2.6 lb [1.2 kg]
Included in Package	1 - vertical wall mount bracket
Included in Package	8 - M5 cage nuts
Included in Package	8 - M5 screws
Included in Package	6 - wood screws
Included in Package	1 - installation manual

Certifications, Reports and Compatibility

