

## 3U 19in Steel Vertical Wall Mount Equipment Rack Bracket

StarTech ID: RK319WALLV



The RK319WALLV 3U 19in Steel Vertical Wall Mount Equipment Rack Bracket offers a versatile storage solution, allowing equipment (Network devices, power strips, patch panels) to be mounted vertically (flush with wall) to save space. Alternatively, the 3U bracket can be installed under a desk for horizontal installation, making it easy to access installed equipment directly from your workspace.

Constructed to EIA-310 19in rack standards, the wallmount bracket features a sturdy steel design, perfect for SoHo (small office, home office) environments. The wallmount bracket offers space-saving installation for environments lacking the footprint space for a full size server equipment rack.

Suitable for mounting on virtually any wall/ceiling surface (e.g. drywall), the bracket mounting holes (used to mount to a wall or the desk underside) are positioned at exactly 16in apart, matching standard construction framework.

Backed by a StarTech.com lifetime warranty.

Need more storage space? StarTech.com also offers a [1U 19in Wallmount Bracket](#), a [2U 19in Wallmount Bracket](#) and a [4U 19in Wallmount Bracket](#).

### Applications

- Mount networking and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space
- Ideal for small and medium businesses needing rack solutions

## Features

- Constructed to meet the EIA-310 19" rack standards
- Arrives fully assembled with cage screws and nuts for mounting equipment into the rack
- Equipment can be vertically wall mounted, or horizontally under a desk
- Compatible with most 19" rack mountable equipment
- Made from solid steel for durability
- Wall mounting holes are 16" center to center for greater stability, and mounting to standard wall studs

## Technical Specifications

|                           |  |
|---------------------------|--|
| Warranty                  | Lifetime   |
| U Height                  | 3U   |
| Frame Type                | Open Frame   |
| Wallmountable             | Yes  |
| Front Door Type           | Open   |
| Industry Standards        | EIA RS310-C  |
| Fan(s)                    | No   |
| Weight Capacity           | 125.3 lb [56.7 kg]   |
| Color                     | Black  |
| Internal Width            | 18.3 in [465 mm]   |
| External Width            | 19.8 in [504 mm]   |
| External Height           | 5.9 in [149 mm]  |
| External Depth            | 5.9 in [151 mm]  |
| Product Weight            | 33.2 oz [940 g]  |
| <b>Note</b>               | Package includes 1 ½" screws for mounting to wood surfaces, additional hardware will be required for other materials |
| Flat Pack                 | No   |
| Shipping (Package) Weight | 3.1 lb [1.4 kg]  |
| Included in Package       | 1 - Vertical Wall Mount Bracket  |
| Included in Package       | 12 - Cage nuts and screws (12 Each)  |
| Included in Package       | 6 - Self Tapping Wood Screws - 3/16" x 1 1/2"  |

Certifications, Reports and Compatibility

