

Product data sheet

Specifications



Rack PDU, Basic, Zero U, 15A, 100/120V, (14) 5-15

AP9567

Overview

Presentation APC Basic Rack PDUs distribute reliable rack power distribution via a single input with multiple output receptacles. Easily mount this vertical PDU in racks or enclosures. It occupies zero U of valuable rack space, which allows space for more equipment in the rack. This vertical PDU does not require additional tools to mount into APC NetShelter Enclosures. Enables a quick recovery from overload events. Packaging Includes PDU, Installation guide, Rack Mounting brackets, Toolless Mounting Kit.

Lead time Usually in Stock

Main

Color Black

Product or Component Type PDU

PDU Type Basic

Cord length 12 ft (3.7 m)

Number of cables 1

Provided Equipment Installation guide
Rack Mounting brackets
Toolless Mounting Kit

Complementary

Input Voltage 100 V
120 V

Height 24.02 in (61 cm)

Width 1.7 in (4.4 cm)

Output Voltage 100 V
120 V

Depth 1.7 in (4.4 cm)

Net Weight 4.81 lb(US) (2.18 kg)

mounting location Side

Mounting preference No preference

Input Plug Type NEMA 5-15P

Mounting Mode Rack-mounted

Rack units 0U

mounting position Vertical

Line Rated Current 12 A

Acceptable Input Voltage 100...125 V

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Input current limits	15 A
Load Capacity	1400 VA
Input Frequency	50/60 Hz
Outlet type and quantity	14 NEMA 5-15R

Environment

Product Certifications	cUL Listed METI Denan UL Listed
Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Ordering and shipping details

GTIN	731304207061
Country of origin	IN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	25.5 in (64.8 cm)
Package 1 Width	6.0 in (15.2 cm)
Package 1 Length	7.008 in (17.8 cm)
Package 1 Weight	6.44 lb(US) (2.92 kg)

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

 Energy Efficient Product

 Take-Back Program Available

Well-being performance

 Lead Free

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov