

Specifications

Photo is representative

Eaton T2235-F4-CFB09L

Eaton ATS rack PDU, 1U, (2) L6-30P input, 4.99 kW max, 208-240V, 24A, 9 ft cord, Single-phase, Outlets: (4) C13, (2) C19

General specifications

PRODUCT NAME	Eaton ATS PDU
CATALOG NUMBER	T2235-F4-CFB09L
UPC	786680223822
PRODUCT LENGTH/DEPTH	20 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	25 in
PRODUCT WEIGHT	10 lb
WARRANTY	3 year
COMPLIANCES	Contact Manufacturer
CERTIFICATIONS	UL Listed

Physical

MOUNTING DIRECTION	Horizontal
COLOR	Black
FORM FACTOR	1U
OPERATING TEMPERATURE	0° to 60°C (32° to 140°F)

Electrical output

OUTLETS	(4) C13, (2) C19
CIRCUIT BREAKER	(2) 2P 15A
OUTLET CONTROL	No

Resources

DRAWINGS	Eaton eATS T2235-F4-CFB09L technical drawing
MANUALS AND USER GUIDES	Eaton T2235 series eATS ePDU
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - T2235-F4-CFB09L

Electrical input

INPUT CONNECTION	(2) L6-30P
CORD LENGTH	9 ft
WATTAGE	4.99 kW max
AMPERAGE RATING	24A
INPUT VOLTAGE	208-240V
PHASE	Single-phase
FREQUENCY RATING	50-60 Hz

Additional specifications

SERIES	eATS
---------------	------

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

