

6ft (1.8m) UK Computer Power Cable, 18AWG, BS 1363 to C13, 10A 250V, Black Replacement AC Power Cord, Kettle Lead / UK Power Cord, PC Power Supply Cable, TV/Monitor Power Cable

Product ID: PXT101UK



This standard 6ft (UK) computer power cord features durable, high quality construction and is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Plugs monitor, PC, or laser printer into a grounded U.K. power outlet

Features

- **AC POWER CABLE:** This 6ft (1.8m) 18AWG (0.75mm²) flexible computer power cable with BS 1363 and IEC 60320 C13 connectors is suitable for workstation/home office use Rated to carry 250V at 10A
- **PERFORMANCE AND SAFETY:** Fully molded strain relief for durability and VDE approved connectors 3 Conductor Power Cable made from 100% Copper Wire Fire Rating: VW-1
- **SPECS:** 6ft (1.8m) Power Cord BS 1363 to IEC 60320 C13 18AWG (0.75mm²) 250V 10A (Max) Jacket Rating: H05VV-F Jacket Material: PVC Color: Black Temperature Range: 3 to 60 Cable Outer Diameter: 6.8mm
- **COMPATIBILITY:** BS 1363 works with UK electrical outlets IEC C13 connector works with most desktop

computers, monitors, printers, and many more Replacement PC power supply cable/cord, Kettle Lead

• THE IT PRO'S CHOICE: Designed for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance This UK power cord is available in other lengths

Hardware

| | |
|-----------------------|--------------------------|
| Warranty | Lifetime |
| Number of Conductors | 3 |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Cable Type | SVT |

Performance

| | |
|------------------------|--------------------------|
| General Specifications | In-Plug Fuse Rating: 13A |
|------------------------|--------------------------|

Connector(s)

| | |
|-------------|-------------------------|
| Connector A | 1 - BS 1363 Power (UK) |
| Connector B | 1 - IEC 60320 C13 Power |

Power

| | |
|---------------|--------|
| Input Voltage | 250 AC |
| Input Current | 10 A |

Physical Characteristics

| | |
|-------------------|---------------------|
| Color | Black |
| Wire Gauge | 0.75mm ² |
| Cable Length | 6.0 ft [1.8 m] |
| Product Length | 6.0 ft [1.8 m] |
| Product Width | 0.0 in [0.0 mm] |
| Product Height | 0.0 in [0.0 mm] |
| Weight of Product | 8.1 oz [230.3 g] |

Packaging Information

| | |
|------------------|---|
| Package Quantity | 1 |
|------------------|---|

| | |
|---------------------------|------------------|
| Package Length | 8.7 in [22.0 cm] |
| Package Width | 7.9 in [20.0 cm] |
| Package Height | 1.9 in [4.9 cm] |
| Shipping (Package) Weight | 8.4 oz [239.3 g] |

What's in the Box

| | |
|---------------------|----------------------|
| Included in Package | 1 - 2m PC Mains Lead |
|---------------------|----------------------|

**Product appearance and specifications are subject to change without notice.*