

# Eaton EHBPL3000R-PDU1U

Catalog Number: EHBPL3000R-PDU1U

Eaton Basic rack PDU, 1U - EHBPL3000R-PDU1U

## General specifications

Product Name	Catalog Number
Eaton HotSwap MBP	EHBPL3000R-PDU1U
UPC	Product Length/Depth
743172067364	17.3 in
Product Height	Product Width
2.1 in	3.8 in
Product Weight	Warranty
0.0001 lb	3 year
Compliances	Certifications
Contact Manufacturer	UL Listed



## Product specifications

### Outlet control

No

### Cord length

1m

### Phase

Single-phase

### Input voltage

110-125V

### Color

Black

### Wattage

2.88 kW max

### Form factor

2U

### Mounting direction

Horizontal

### Amperage Rating

24A

### Input connection

L5-30P

### Outlets

(5) 5-20R

### Type

PDU

### Frequency rating

50-60 Hz

### Number of Outputs 5-20R

5

### Operating Temperature

0° to 60°C (32° to 140°F)

### Circuit breaker

(2) 20A

## Resources

### Brochures

[Eaton Flex and Hotswap MBP ePDU brochure](#)

### Drawings

[Eaton FlexPDU EHBPL 3000R-PDU1U technical drawing](#)

[Eaton ePDU visio stencils](#)

### Specifications and datasheets

[Eaton Specification Sheet - EHBPL3000R-PDU1U](#)

### User guides

[Eaton FlexPDUs and HotSwap MBP installation and user manual](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)