



16-port Cat6 Unshielded Patch Panel

TC-P16C6 (2.0)

- · Gigabit ready rack mount 16-port panel
- Cat6 patch panels deliver a steady 250Mhz connection to copper Gigabit switches
- Ideal solution for Ethernet, Fast Ethernet and Gigabit applications
- Use with TRENDnet TC-PDT Punch Down Tool

Prepare yourself for Copper Gigabit Ethernet with TRENDnet's Cat. 6 RJ-45 UTP Patch Panels. These patch panels are certified for 250Mhz Category 6, which are perfect for Copper Gigabit Ethernet connections. TRENDnet's 16-port Cat. 6 Patch Panels are ideal for Ethernet, Fast Ethernet and Copper Gigabit Ethernet (1000Base-T) network applications. Using TRENDnet's Cat. 6 products now, will prepare you for the high bandwidth network in the future without re-cabling your network.



- Meets ANSI/EIA/TIA 568-B.2-1 and ISO/IEC 11801 Standards
- New version 110D IDC type terminal blocks (use 110 or Krone type tool)
- Color-coded labeling for T568A and T568B wiring schemes
- 180° angle type (horizontal)
- 1000Base-T Copper Gigabit Ethernet ready
- Compatible with Cat. 3, 4, 5, 5e, and 6 cabling
- Works perfectly with TC-PDT Punch Down Tool
- Operating temperature: -40° ~ 80° C (-40° ~ 176° F)
- UL E157358 listed
- 1-year limited warranty