



Professional print, copy and scan from your desktop

The MB260 is a smart, compact, multifunctional device which will deliver professional looking A4 documents in an instant. It prints and copies in mono at 20 pages per minute, whilst the colour scanner ensures your important documents can be stored, amended and communicated electronically.

Add to this OKI Printing Solution's unique 3 year warranty and competitive running costs and the MB260 offers both peace of mind and real value for money.

For high productivity working at home or in the office let the MB260 get to work for you.

Efficient and Versatile

- Provides mono printing, copying and colour scanning
- Its compact design fits neatly on your desk
- Quick and easy to set up and operate
- A flatbed scanner makes copying bound documents such as books and reports simple
- Digital copying with zoom and multi-copy features
- Supports a range of media including address labels, CD labels, letters and envelopes

Highly productive

- 20ppm printing and copying keeps business moving
- A 250 sheet paper tray means less time reloading and more time printing
- Changing the single piece print cartridge is quick, clean and easy
- Convenient front USB port with 'scan to' and 'print from' functionality allows easy transfer and sharing of documents using a USB memory device
- Supports MS Windows (including Vista), MAC and Linux operating systems

Expect more from your MFP

- Quickly configure, program and manage the MB260 from the comfort of your chair with Companion Suite Pro software (Windows only)
- PaperPort software makes cleaning, editing and saving scanned documents in different formats quick and easy.
- A wireless interface option provides easy connection and sharing flexibility



MB260
A4 print, copy
and scan



The MB260 mono multifunction product

		MB260
Order number		01238701
Speed & throughput	A4 Print speed	20ppm
	Time to first print	13 seconds
	Warm up time	21 seconds
	Processor speed	100MHz
	USB host	Print direct from front USB port
Scan		Type: Colour and mono; Resolution: 600 x 600 dpi (optical), 600 x 2400 dpi (interpolated); Speed: 3.9 seconds from flatbed; Colour depth: 36 bit colour with 256 greyscale; Document input: Flatbed scanner; Contrast: 7 level adjustment; USB host: Scan direct to front USB port; Scan to: PC with PaperPort® supplied software, TWAIN scan
Copy		First copy out: 13 seconds; Speed: 20cpm; Resolution: 600 x 600 dpi; Reduction/Enlargement: 25% to 400%; Maximum copies: 99; Duplex copying: Manual duplex
Print quality	Resolution	600 x 600 dpi
Compatibility	Printer languages	GDI
	Connectivity	USB 2.0 (full speed), USB Host, Optional 802.11b/g
	OS Compatibility ¹	Windows® 2000 SP3, XP, Vista 32/64; Windows server 2003 for printing only; MAC OS (10.3-10.5), Linux
	Access control	Password protection for access control and keyboard lock
Memory	RAM	32MB
	Page memory	2MB
Utilities ¹	Document management	PaperPort®
Paper handling	Paper capacity	Up to 250 sheets
	Paper sizes	Tray: A4, A5, B5 ² , B6 ² , Manual feed: A4, A5, B5 ² , B6 ² , Transparencies, Envelopes, Official Postcard, Custom: (Width 90 - 148mm, Length 216 - 356mm)
	Paper weight	Tray: 60–105 gsm, Manual feed: 52–162 gsm
	Paper output	50 sheets face down
Operating conditions	Temperature/Humidity	10°C to 32°C / 20% to 80% RH non-condensing
	Storage	-20°C to 40°C / 20% to 80% RH non-condensing
	Noise level	Operating: 53dB(A) or less; Stand-by: 30dB(A) or less; Power Save: No acoustic noise
Power requirements	Power supply	220–240V +/- 10%; 50/60Hz +/- 3%
	Power consumption	Operating 340W; Stand-by 13W; Power Save 10W
Dimensions (HxWxD)		344 x 447 x 386mm
Weight ³		11.6kg
Duty cycle	Printer duty (average)	1,500 - 2,000 pages/month
Warranty		3 years extended warranty upon registration within 30 days of purchase ⁴
Accessories	Wireless LAN	Optional (01240101)

¹ Check local OKI Printing Solutions website for latest driver releases & OS Compatibility

² Print only

³ Includes all consumables

⁴ To qualify for the extended 3 year warranty, register your product online at www.okiprintingsolutions.co.uk/warranty. Without registration, the standard pan-European 1 year warranty applies.

Specification subject to change without notice. All trademarks acknowledged.

Consumables

For the protection of your printer, and in order to ensure that you benefit from its full functionality, this model has been designed to operate only with genuine OKI Printing Solutions toner cartridges. These can be identified by the OKI trademark. Any other toner cartridge may not operate at all, even if it is described as “compatible”, and if it does work, your printer's performance and print quality may be degraded.

Description	Life (pages)	Order Numbers
Toners cartridge*	3,000	01239901
	5,500	01240001

* All toners: A4 pages yield compliant with ISO/IEC 19752 coverage. Printer shipped with 2,000 pages yield at ISO/IEC 19752 coverage.



OKI SYSTEMS (UK) LTD.
 550 Dundee Road, Slough
 Berkshire, SL1 4LE
 United Kingdom
 T +44(0) 1753 819819
 F +44(0) 1753 819899
WWW.OKIPRINTINGSOLUTIONS.CO.UK

OKI
 PRINTING SOLUTIONS