

Specifications

Eaton PC975-LT

Eaton REPO Rack PDU: This product has reached end-of-life. For a plug, outlet and physical drop-in replacement, see product sku PC975-LTR

General specifications

PRODUCT NAME	Eaton REPO Rack PDU
CATALOG NUMBER	PC975-LT
UPC	786685287010
PRODUCT LENGTH/DEPTH	0.01 in
PRODUCT HEIGHT	0.01 in
PRODUCT WIDTH	0.01 in
PRODUCT WEIGHT	0.01 lb
COMPLIANCES	Contact Manufacturer
CERTIFICATIONS	Contact Manufacturer

Physical

MOUNTING DIRECTION	Horizontal
COLOR	Black
FORM FACTOR	2U

Electrical input

INPUT CONNECTION	L21-30P
CORD LENGTH	15 ft
WATTAGE	8.64 kW max
AMPERAGE RATING	24A
INPUT VOLTAGE	120/208V WYE
PHASE	Three-phase WYE
FREQUENCY RATING	50-60 Hz

Electrical output

OUTLETS	(8) 5-20R, (3) L6-20R
CIRCUIT BREAKER	4P 30A, 1P 20A, (3) 2P 20A
OUTLET CONTROL	No

Additional specifications

OPERATING TEMPERATURE	0° to 60°C (32° to 140°F)
SERIES	RE

Resources

DRAWINGS	Eaton ePDU REPO PC975-LT technical drawing
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - PC975-LT

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

