

Select Server Cabinets

**Fully assembled
and ready to secure
your data center**




FEATURES

- » Sturdy, attractive, and secure server space at a great price!
- » Has a 2200-lb. capacity
- » Standard 19" M6 rails mean you can use most BLACK BOX® Cabinet Accessories.
- » Available in three heights with mesh or tempered glass doors
- » Solid construction with a fully welded frame
- » Arrives fully assembled and ready to go to work in your data center
- » Keyed door locks and locking side panels
- » Removable side panels
- » Vented top panel
- » UL® Listed
- » Generous cable access
- » Powder black finish
- » Includes 2.5" casters and leg levelers



6-Fan Unit
(RM2415)



RM2400A

TECH SPECS

Capacity – 2205 lb. (1000 kg)
Interior Height – RM2400A, RM2410A: 26.3" (66.8 cm);
 RM2420A, RM2430A: 66.5" (168.9 cm);
 RM2440A, RM2450A: 73.5" (186.7 cm)
Exterior Height – RM2400A, RM2410A: 30.4" (77.2 cm);
 RM2420A, RM2430A: 70.7" (179.6 cm);
 RM2440A, RM2450A: 77.6" (197.1 cm)
Interior Width – 21.3" (54.1 cm)
Exterior Width – 23.6" (59.9 cm)
Interior Depth – 38.5" (97.8 cm)
Exterior Depth – 39.4" (100.1 cm)

What's included

- 2.5" casters
- Leg levelers
- Tempered glass or mesh front door
- Mesh rear door

Item	Code
Select Server® Cabinets	
15U	
Mesh Door	RM2400A
Tempered Glass Door	RM2410A
38U	
Mesh Door	RM2420A
Tempered Glass Door	RM2430A
42U	
Mesh Door	RM2440A
Tempered Glass Door	RM2450A
Select Server Cabinet Accessories	
Multicabinet Joining Kit	RM2407
Grounding Kit	RM2408
3-Fan Unit	RM2409
6-Fan Unit	RM2415

