

The definitive wireless & versatile All-in-One photo solution that allows you to print anywhere in your home. Superior prints, copies and scans.

Advanced Range



The PIXMA MP990 is an advanced solution to producing superior prints, copies and scans. Maximum print resolution of 9600dpi combined with microscopic dots of a minimum size of 1pl and 6 efficient individual ink tanks ensure lab quality photos. Print in approximately 20 sec for a 6" x 4" photo³. Advanced features of zero warm up time to save you time when scanning, direct printing from compatible camera, memory cards or mobile phones, direct printing onto a DVD/CD, 35mm film scan, auto duplex, borderless printing and scanning at up to 4800 x 9600 dpi encourage endless creativity.

Key Features

As a Printer

- High quality photos and documents with 1 picolitre FINE print head technology and 9600 x 2400 dpi¹
- Fast document printing at Approx. 11.9ipm in black and 9.1ipm in colour³
- Photo lab quality prints delivered in high speeds of approx 20 seconds³
- Direct photo printing using PictBridge or directly from compatible memory cards and mobile phones⁴
- Borderless printing up to A4⁵
- Wired/wireless LAN connections in addition to USB allowing the printer to be shared

As a Copier

- Faithfully reproduce copies as they are seen with the naked eye with Dual Colour Gamut Processing Technology
- Standalone copying without a computer
- Copy up to 10.5cpm black and 4.3cpm colour³

As a Scanner

- Scan high-quality photos and documents at up to 4800 x 9600 dpi
- Scan 35mm film quickly and easily

Additional Features

- Quick Start feature allows operations virtually the moment the power is turned on
- 2 way paper feeding to reduce time required for changing paper types and increasing paper capacity
- Auto duplex for easy double sided printing
- Wireless/Wired LAN enables printing/scanning from anywhere in your house
- Print photos directly from USB Flash memory

Easy to use Software

- Easy-Photo Print EX produces optimised prints of both portraits and sceneries with Auto Photo Fix technology
- Easy-Web Print EX automatically scales and adjusts web pages to avoid cropped web pages when printing

**9600^{Maximum}
dpi**
**1^{Minimum}
pl**

ChromaLife 100⁺

6 Single Tanks

**3.8" (9.5cm)
TFT**

Easy-Scroll Wheel

**Wi-Fi
CERTIFIED®**

SCAN CCD
4800x9600dpi

DVD/CD Print

35mm Film

Quality images

9600 x 2400 dpi resolution and 1 picolitre FINE print-head technology for high quality photos and documents¹

Long Lasting Prints

Produce long lasting photos over 300 years with a combination of Canon's genuine dye ink and genuine photo papers²

Efficient Individual Ink Tanks

Individual ink tanks saving you time and money, also notifying you when the ink is running out

Sharper Previews

Large 3.8" colour TFT screen allowing preview and image correction before printing

Simple Operation

Easy Scroll Wheel for simple, clear and intuitive operation of the menu

Wireless Printing®

Have the freedom to connect without cables with built in Wi-Fi and Wired LAN

Quality Scanning


Scan high-quality photos and documents at up to 4800 x 9600 dpi

DVD/CD Print

Precise, fast, high-quality direct printing on printable DVD/CD media

35mm Film Scan

Scan and print photos directly from 35mm negatives or positives without the need for a computer



Why print when you can PIXMA?

Unleash your creativity with the Canon PIXMA range. Print lab quality photos. Make your own T-shirt. Create scrapbooks, calendars, stickers, origami and more! With FINE print-head technology, PIXMA delivers superior quality with unsurpassed speed, ease and reliability.

For results you can be proud of, why print when you can PIXMA?

PIXMA MP990

All-in-One Photo Inkjet Printer

Canon
advanced simplicity®

PIXMA MP990 Technical Specifications

Printer Functions	
Min. Ink Droplet Size¹	1 picolitre
Printing Resolution¹	9600 x 2400 dpi
Print Speed³	Black Text : Approx. 11.9ipm, Colour Text & Graphics : Approx. 9.1ipm, 6"x4" Standard Borderless Photo : Approx. 20 secs
Ink Tanks	PGI-520BK, CLI-521BK, CLI-521C, CLI-521M, CLI-521Y, CLI-521GY
Ink Yield⁴	Borderless 6x4" photo PGI-520BK (approx 2920), CLI-521BK (approx 580), CLI-521C (approx 289), CLI-521M (approx 269), CLI-521Y (approx 247), CLI-521GY (approx 178)
	Plain paper A4 PGI-520BK (approx 322), CLI-521BK (approx 1250), CLI-521C (approx 448), CLI-521M (approx 445), CLI-521Y (approx 477), CLI-521GY (approx 1370)
Borderless Printing	6"x 4", 5"x 7", 8"x10", Letter, A4,
Plain Paper Capacity	300 sheets
Supported Paper Sizes	A4, Letter, Legal, A5, B5, Envelopes(DL, COM10), 4"x6", 5"x7", 8"x10",
Supported Paper Weights	Plain Paper: 64-105g/m². Canon specialty paper (max paper weight): approx 300g/m² (Photo Paper Pro Platinum PT-101)
Wired LAN Protocol	TCP/IP
Wired LAN Network Type	IEEE802.3u (100BASE-TX)/IEEE802.3 (10BASE-T)
Wired LAN Transmission System	100M/10Mbps (auto switchable)
Wireless LAN Network Type⁶	IEEE802.11g/IEEE802.11b + IEEE802.11n (transmission rate will be limited to IEEE802.11g and operate in the 2.4Ghz frequency band)
Wireless LAN Transmission System	OFDM/DS-SS System
Wireless LAN Range	Indoor 50m (depends on the transmission speed and condition)
Wireless LAN Standard⁶	Wi Fi, FCC, IC, ETSI, iDA
Wireless LAN Security	WPA-PSK, WPA2-PSK, TKIP/AES, WEP64/128bit, Administration password
Camera Direct Printing⁵	PictBridge (connect your iXUS, Powershot, EOS, Legria or other compatible camera)
Direct Memory Card & USB Flash Memory Printing⁵	Yes/Yes
Mobile Phone Printing⁵	PictBridge, IrDA 1.2 Infra Red + optional Bluetooth with BU-30 adaptor
CD/DVD Printing	Yes, using Printable DVD/CDs
Auto Duplex Unit	MP990 prints double sided as standard
Copier Functions	
Speed	Black Text : Up to 10.5cpm, Colour : Up to 4.3cpm
Multiple Copy	Up to 99 copies
Reduction/Enlargement	25% to 400%
Special Copy Functions	Fit-to-page
Scanner Functions	
Scanner Type	CCD (Charge Coupled Device)
Scanning Resolution	4800 x 9600 dpi
Colour Scanning Depth	48 bit input/24 bit output
Film Scan	35mm x 6 frames (negative/positive film), 35mm x 4 frames (mounted slides)
Special Scanning Functions	Push Scan, Network Scan
General Features	
Colour LCD Screen	3.8 inch
Automatic Document Feeder	N/A
Dual Paper Path	Available
Easy Scroll Wheel	Available
PC Interface Type⁶	USB (B Port) Hi-Speed, Bluetooth v 2.0 and Bluetooth enabled computer, Wired LAN
Operating System	PC: Windows Vista SP1 32bit/64bit; XP/SP2/SP3; 2000,2000 Professional SP4, Mac: OS.X (10.3.9 or later)
Included as Standard	PIXMA MP990 All-in-One printer, Setup CD-ROM and printed documents, 6 Canon genuine ink tanks, CD-R tray & CD-R adaptor, paper for print alignment, USB cable, power cord and 12 month warranty card
Software Included	Easy-PhotoPrint EX, Easy-PhotoPrint Pro, Easy WebPrint EX (IE7 only), MP Navigator EX, CD Label Print
Power Source	AC 100-240V, 50/60Hz
Power Consumption	Max: 23W (copying), Standby: 1.7W
Min. Dimensions (W x D x H)	470 x 385 x 199 mm
Weight	Approx. 10.7kg

Disclaimers

- Ink droplets can be placed with a pitch of 1/9600 inch at minimum.
- Up to 300 Years' Life in a Photo Album when printed with ChromaLife100+ ink on selected Canon photo papers. Kept in a photo album, shut out light and air (gas), temperature 23 degrees and 50% humidity. Predicted value from the accelerated test. Result may vary based on individual environmental factors. For more information, please visit canon.com.au/ChromaLife100+
- Document print speeds are the averages of ESAT in Office Category Test for the default simplex mode, ISO/IEC 24734, excluding time to print the first set. Photo print speed is based on the default setting using ISO/JIS-SCID N2 on 4x6" Photo Paper Plus Glossy II and does not take into account data processing time on host computer. Print speed may vary depending on system configuration, interface, software, document complexity, print mode, page coverage, type of paper used etc.
- PictBridge camera direct and mobile phone printing requires PictBridge compatible digital cameras and phones in order to function. Check with your manufacturer or users guide to determine PictBridge compatibility.
- Supported paper types for borderless printing: Photo Paper Pro, Photo Paper Plus Glossy, Photo Paper Plus Semi-gloss, Glossy Photo Paper, Matte Photo Paper, Photo Paper Plus Double-side
- A computer that complies with Hi-speed USB standard and/or Wi-Fi is required

Subject to change without notice.



Consumables



Semi-Gloss Photo Paper (SG201)

Archival-quality, super high-gloss photo paper for professional results



Photo Paper Plus Glossy (PP201)

Premium high gloss paper for brilliant photo prints



Canon Extended Warranty

Extended warranty is available on this product. Peace of mind for three years. Call 13 13 83



*Ink yield value in accordance with ISO/IEC 24711.
Plain paper values obtained by continuous printing.
6x4 photo paper values obtained by continuous printing.
The figures above are an average value, measured when printing continuously using the ink immediately after it is unsealed, until the ink is out. Ink yield may vary depending on photos/documents printed, applications software used, print mode and type of paper used. This should be used as a guide only and does not take into account ink that might be used for head cleaning or head refreshing to maintain printer performance. Please visit our website for further details.

canon.com.au