

1ft (30cm) Power Extension Cord, IEC 320 C14 to NEMA 5-15R, 10A 125V, 18AWG, Black  
Computer Power Extension Cord, AC Outlet Extension Cable for Power Supplies/PDUs/ Network  
Equipment, UL Listed

**Product ID:** PAC100



The PAC100 1ft Computer Power Cord/Cable enables you to use the switched source on your PC to power your monitor or printer.

Expertly designed and constructed of high quality materials, this C14 to NEMA 5-15R cable features one hooded (male) power connector and one computer power (female) connector.

This high quality computer power cable is backed by our Lifetime Warranty.

## Certifications, Reports and Compatibility



## Applications

- Allows monitor or printer to draw power from the switched source on the PC

## Features

- **AC COMPUTER POWER CABLE:** This 1ft (0.3m) 18AWG AC power extension cable with IEC 60320 C14 to NEMA 5-15R connectors is suitable for workstations/home office Indoor use Rated to carry 125V at 10A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief connectors for durability Fire

Rating: VW-1 3 Conductor extension cord made with 100% copper wire This C14 to 5-15R power extension cord is available in other lengths

- **SPECS:** 1ft (0.3m) AC Power Cord IEC 60320 C14 to NEMA 5-15R 18AWG 125V 10A (Max) Jacket Type: SVT Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.24in (6.1mm)

- **COMPATIBILITY:** PC Power Extension Cord NEMA 5-15R works with North American cables Extend a 3-prong power connection from your desktop computer, server, or printer Replacement power supply cable/cord

- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

---

**Connector(s)**

Warranty	Lifetime
Connector A	1 - IEC 60320 C14 Power
Connector B	1 - NEMA 5-15 Power (North America)

---

**Special Notes / Requirements**

Note	UL Listed
------	-----------

---

**Power**

Input Voltage	125 AC
Input Current	10 A

---

**Environmental**

Operating Temperature	-20 to 60 C
Storage Temperature	-20 to 60 C
Humidity	0 to 70%

---

**Physical Characteristics**

Color	Black
Wire Gauge	18 AWG
Cable Length	1.0 ft [0.3 m]
Product Length	1.0 ft [0.3 m]
Product Width	1.4 in [3.5 cm]
Product Height	1.0 in [2.5 cm]



Weight of Product	2.5 oz [71.0 g]
-------------------	-----------------

---

**Packaging Information**

Package Length	8.7 in [22.0 cm]
----------------	------------------

Package Width	7.9 in [20.0 cm]
---------------	------------------

Package Height	1.4 in [36.0 mm]
----------------	------------------

Shipping (Package) Weight	2.8 oz [80.0 g]
---------------------------	-----------------

---

**What's in the Box**

Included in Package	1 - 1 Ft. Monitor Power Adaptor
---------------------	---------------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

