

20 ft DVI-D Dual Link Cable - M/M

StarTech ID: *DVIDDMM20*



The DVIDDMM20 20ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and offers 20 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 20 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Technical Specifications

Warranty	Lifetime
Connector Plating	Nickel
Cable Shield Type	Aluminum-Mylar Foil with Braid
Industry Standards	DVI DDWG Standard
Connector A	1 - DVI-D (25 pin) Male
Connector B	1 - DVI-D (25 pin) Male
Color	Black
Wire Gauge	28 AWG
Cable Length	6.1 m [20 ft]
Product Length	6.1 m [20 ft]
Product Weight	0.8 kg [1.7 lb]
Shipping (Package) Weight	0.8 kg [1.7 lb]
Included in Package	1 - 20 ft DVI-D Dual Link Cable - M/M

Certifications, Reports and Compatibility

