

USB VGA over Cat5 UTP KVM Console Extender Kit - 500 ft. (152.4 m)

MODEL NUMBER: **ODT60001**



Features

- Compatible with any KVM switch / computer
- Extends console (USB keyboard, USB mouse and VGA monitor) up to 150m / 500ft from computer, KVM or server
- Integrated local port for local keyboard, mouse and monitor
- 2 port KVM switch built into remote unit
- Pure hardware solution - no software/network conflicts
- Supports high-resolution video - up to 1600 x 1200 @ 75 Hz
- All cables included - off-the-shelf retail package, easy to maintain
- Simple to install and operate
- No external power needed at transmitter end
- Supports all major OS
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Extends console (USB keyboard, USB mouse and VGA monitor) up to 150m / 500ft from computer, KVM or server
- Integrated local port for local keyboard, mouse and monitor
- 2 port KVM switch built into remote unit
- Supports high-resolution video - up to 1600 x 1200 @ 75 Hz
- All cables included - off-the-shelf retail package, easy to maintain
- No external power needed at transmitter end
- Supports all major OS
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- Compatible with all major operating systems
- Compatible with any KVM switch / computer
- USB Keyboard and Mouse
- PS/2 Keyboard and Mouse with ODT60002 PS/2 to USB Converter
- When using the ODT60001 to extend the console ports of a KVM switch, the transmitter unit may require an external power supply. Use a 12VDC 1A power supply.

Package Includes

- Local Transmitter Unit
- Remote Receiver Unit



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- (x2) VGA + USB KVM Cable Kits
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz Output: 12V/1000mA) and Plug Adapters for US, UK, Europe and Australia, NEMA
- Screwdriver
- Rubber Feet
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	654518302196
Technology	USB; VGA/SVGA
VIDEO	
Max Supported Video Resolution	1600 x 1200 @75Hz
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	NEMA 5-15P North America; CEE 7/16 Schuko; BS 1363 UK; AS/NZS 3112 Australia
Bus Powered	Yes
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.5A
External Power Supply Output Specs (V / A)	12V / 1A
External Power Supply Cord Length (ft.)	6
External Power Supply Cord Length (m.)	1.8
External Power Supply Certifications	CE; UL; CCC; PSE; C-Tick; GS; RoHS
USER INTERFACE, ALERTS & CONTROLS	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

LED Indicators	TX: Green (Control), Red (Lock) RX: Green (Local), Red (Lock)
PHYSICAL	
Color	Gray
Material of Construction	Steel
Receiver Unit Dimensions (hwd / cm.)	2.9 x 6.9 x 16.5
Receiver Unit Dimensions (hwd / in.)	1.1 x 2.7 x 6.5
Receiver Unit Weight (kg)	0.28
Receiver Unit Weight (lbs.)	0.61
Shipping Dimensions (hwd / cm)	10.41 x 20.32 x 31.50
Shipping Dimensions (hwd / in.)	4.10 x 8.00 x 12.40
Shipping Weight (kg)	1.72
Shipping Weight (lbs.)	3.80
Transmitter Unit Dimensions (hwd / cm.)	2.9 x 6.9 x 16.5
Transmitter Unit Dimensions (hwd / in.)	1.1 x 2.7 x 6.5
Transmitter Unit Weight (kg)	0.27
Transmitter Unit Weight (lbs.)	0.58
Unit Packaging Type	Box
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-40 to 158 F (-40 to 70 C)
Relative Humidity	0% to 80% RH, Non-Condensing
BTUs	40.9 BTU/Hr
Power Consumption (Watts)	12
COMMUNICATIONS	
Signal Range (ft.)	500
Signal Range (m)	152
EDID Compatible	Yes
CONNECTIONS	
Ports	2
PC/Server Connections	VGA; USB; PS/2
Side A - Connector 1	(2) HD15 (FEMALE); RJ45 (FEMALE); (2) USB A (FEMALE)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Side B - Connector 1	(2) HD15 (FEMALE); RJ45 (FEMALE); (2) USB A (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
Port Selection	Pushbutton
Recommended Category Cable	Cat5/Cat5e/Cat6
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH, C-Tick, Canada ICES
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>