

# Product data sheet

Specifications



## Rack PDU, Basic, Zero U, 20A, 120V, (24)5-20

AP7530

**Product availability: Stock - Normally stocked in distribution facility**

### Overview

**Lead time** Usually in Stock

### Main

**Color** Black

**Product or Component Type** PDU

**PDU Type** Basic

**Cord length** 10 ft (3.05 m)

**Number of cables** 1

**Provided Equipment**  
Cord retention bracket(s)  
Installation guide  
Rack Mounting brackets  
Toolless Mounting Kit  
User Manual

### Complementary

**Input Voltage**  
100 V  
120 V

**Height** 63.7 in (161.9 cm)

**Width** 2.2 in (5.6 cm)

**Output Voltage** 120 V

**Depth** 1.7 in (4.4 cm)

**Net Weight** 10.71 lb(US) (4.86 kg)

**mounting location** Side

**Mounting preference** No preference

**Input Plug Type** NEMA L5-20P

**Mounting Mode** Rack-mounted

**Rack units** 0U

**Mounting position** Vertical

**Line Rated Current** 16 A

**Acceptable Input Voltage** 100...120 V

**Input current limits** 20 A

**Load Capacity** 1920 VA

**Input Frequency** 50/60 Hz

**Outlet type and quantity** 24 NEMA 5-20R

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Environment

<b>Product Certifications</b>	cUL Listed UL Listed
<b>Standards</b>	CSA C22.2 No. 60950-1-03 UL 60950-1
<b>Ambient Air Temperature for Operation</b>	23.0000000000...113.0000000000 °F (-5...45 °C)
<b>Relative Humidity</b>	5...95 %
<b>Operating altitude</b>	0...15000 ft
<b>Ambient Air Temperature for Storage</b>	-13.0000000000...149.0000000000 °F (-25...65 °C)
<b>Storage Relative Humidity</b>	5...95 %
<b>Storage altitude</b>	0...50000 ft (0.0000000000...15240.0000000000 m)

## Ordering and shipping details

<b>Category</b>	11309-APC RESALE PRODUCTS
<b>Discount Schedule</b>	APC1
<b>GTIN</b>	731304207962
<b>Returnability</b>	No
<b>Country of origin</b>	IN

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	84.02 in (213.4 cm)
<b>Package 1 Width</b>	5.0000000000 in (12.7 cm)
<b>Package 1 Length</b>	6.0 in (15.2 cm)
<b>Package 1 Weight</b>	12.72 lb(US) (5.77 kg)
<b>SCC14</b>	731304207962

## Contractual warranty

<b>Warranty</b>	2 years repair or replace
-----------------	---------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Energy Efficient Take-back Transparency RoHS/REACH

## Resource performance

 Energy Efficient Product

 Take-Back Program Available

## Well-being performance

 Lead Free

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)