



FSW-2450 Version: 5



24-Port Fast Ethernet Switch

Product Overview The FSW-2450 switch provides an ideal solution for small businesses that demand a reliable network switch that provides a high bandwidth interface between file servers and workgroups, departments and offices.

Advanced Networking Features The LevelOne FSW-2450 is a wire-speed, nonblocking 24 port Fast Ethernet Unmanaged Switch with an internal power supply. It provides a network with an 8K MAC address table, 4.8Gbps backplane throughput, asymmetrical flow-control support for full-duplex network connectivity, auto-negotiation and Auto-MDIX.

The 24-port Fast Ethernet Switch utilizes packet store-and-forwarding switching for error-free data transmissions and IEEE802.3x backpressure flow control to control data flow between the sending and receiving nodes as well as to prevent any data packet loss.

Compact Design The FSW-2450 is a compact designed network switch. Users can place the switch on any desktop area or mount it in a 19-inch server rack or cabinet by using the included rack-mounting accessory kit.

Quick Configuration and Easy Maintenance The LevelOne FSW-2450 does not require any software configuration. It is Plug-and-Play enabled for quick set-up and immediate use within the Local Area Network. The 24 port Fast Ethernet Switch is equipped with a full range of LEDs for instant error detection, networking monitoring and network troubleshooting.

Key Features

- Provides flexibility of 24 x 10/100BASE-TX ports
- 10/100Mbps, full/half-duplex, auto-negotiation, auto-MDI/MDIX
- Supports 8K MAC address auto-learning and auto-aging
- IEEE 802.3x Flow Control protects against lost packets for reliable data transmission
- 19-inch metal housing

Specifications

System Specifications

Standards:

- IEEE802.3(10BASE-T)
- IEEE802.3u(100BASE-T)
- IEEE802.3az Energy Efficient Ethernet



Buffer Memory:

2MB

Port:

24 x 10/100BASE-TX RJ45 ports

Indicator:

Power, LINK/ACT

Transmission Method:

Store- forward

Power Input:

100-240V/AC?50-60Hz

Power Consumption:

6.6W

Backplane (Gbps):

4.8Gbps

MAC Address Table:

8K

Power Saving:

YES

Operating Temperature (°C):

Operating: 0°C ~ 50°C

Storage: -40°C ~ 70°C

Operating Humidity (Non-condensing):

Operating: 10% ~ 90%

Storage: 5% ~ 95%

Features

General:

24 x 10/100BASE-TX RJ45 ports

Performance

Packet Forwarding Rate:

14880pps

Jumbo Frame (K):

2KB

Physical Specifications

Dimensions (W x D x H mm):


441 x 208 x 44

Approval and Compliance

EMI/EMS:

CE/FCC

Diagram



Order Information

FSW-2450

Package Contents

FSW-2450
Power Cord
19" Rack Mount Kit

No liability or responsibility for any errors or omissions in the content.
Specifications are subject to change without notice.
All mentioned brand names are registered trademarks and property of their owners.
Copyright © Digital Data Communications GmbH, Germany. All Rights Reserved.