

Mountable Rugged Industrial 7 Port USB Hub

StarTech ID: ST7200USBM



This sturdy, industrial grade USB hub can be wall mounted or installed onto a DIN rail for convenient access to its 7 female USB ports, providing a work area, server room, or industrial environment with USB 2.0 connectivity.

With support for Hi-Speed USB 2.0 data transfer rates of up to 480 Mbps, this 7 port USB hub is backwards compatible with USB 1.1 specifications and can be powered through the host USB bus, or self powered using a three wire terminal block connector (7-24V).

Applications and Solutions

- Connect your usb devices to this industrial strength USB hub. Wall-mount or install onto a DIN rail to provide convenient access to the USB ports.
- The ST7200USBM ensures that enough power is being provided to your devices. Connect power through 3-pin terminal block (7-24V)

Features

- Choice of Bus Power and/or External Terminal Block Power with support for 7 to 24 Volt power range.
- Compact space saving and mountable design (mount on a wall or DIN rail)
- Maximum data transfer rate of up to 480 Mbps and backwards compatible with USB 1.1
- Quick, easy installation

Technical Specifications

- Warranty: 1 Year warranty
- Color: Black
- Connector Types: 4 - USB A Female
- Connector Types: 1 - USB B Female
- Enclosure Type: Steel
- Product Height: 1.43 in [36.3 mm]
- LED Indicators: 1 - Power
- Product Length: 5.24 in [133 mm]
- Number of Ports: 7
- Operating Temperature: 0°C to 55°C (32°F to 131°F)
- Power Adapter Included: No
- Carton Quantity: 25
- Industry Standards: USB 2.0
- Shipping (Package) Weight: 1.55 lb [0.7 kg]
- Product Weight: 17.65 oz [500 g]
- Product Width: 2.42 in [61.5 mm]
- Data Transfer Rate: Up to 480 Mbits/sec
- Power Input: Terminal Block, 3-Wire connector (7-24 Volts DC)
- Humidity: 5~95% RH
- Storage Temperature: -20°C to 85°C (-4°F to 185°F)
- OS Compatibility: OS independent; No software or drivers required

