



SK-97-TP-BLK

Sealed with Integrated Touchpad

iKey's SK-97-TP-BLK keyboard provides users with all the functionality of a full-size keyboard and mouse in a slim, compact package. It is designed for infection control in today's healthcare environment and for industrial applications. The fully sealed keyboard has an integrated touchpad and is compatible with all hospital-approved disinfectants. The SK-97-TP-BLK features left and right-click buttons below the touchpad, adding convenience and functionality. The durable and easily cleanable SK-97-TP-BLK is ideal for use in ORs, medical carts and industrial workstations.

Features:

- 12 Function Keys
- Cleanable, Liquid-proof Design
- Integrated 10-Key Numeric Pad
- USB configurations available

Product Code SK-97-TP-BLK

Certifications	NEMA 4X, CE UL60950, FCC Part 15 Class B
Shock	3x11 ms pulses of 50g on each of 3 axes
Cable	LENGTH: 10ft
Key Switch	MATERIAL: Industrial silicone rubber LIFE: Greater Than 10 million Cycles TRAVEL: 0.055 in. (1.4mm) ACTUATION FORCE: 7.05 oz +/- 1.06 oz. (200g +/- 30g) FEEDBACK: Tactile with Mechanical Snap
Vibration	POWER SPECTRAL DENSITY: 0.04g/Hz FREQUENCY RANGE: 20Hz - 2 kHz DURATION OF TEST PER AXIS: 3 hours
Power	PS/2: KEYBOARD: 210mA@5V (from Keyboard port) TOUCHPAD: 10 mA@5V (from Mouse port) USB: 220mA@5V (from CPU port)
Compatibility	PS/2 KEYBOARD/TOUCHPAD: All Windows Operating Systems USB KEYBOARD/TOUCHPAD: All Windows and Macintosh OS
Temperature Range	STORAGE: -40C to +90C (-40F to +194F) OPERATING: -40C to +70C (-40F to +158F)
Weight	1.50 lbs +/- 0.10 lbs (0.68 kg +/- 0.05 kg)
Warranty	1 year limited warranty
Humidity	100% Humidity Resistant
Dimensions	14.44" x 5.40" x 0.89" (w-h-d) 366.8mm x 137.2mm x 22.6mm

Model Number SK-97-TP-PS2-BLK: With PS/2 cable SK-97-TP-USB-BLK: With USB cable
