CyberPower



PDU30BHVT8R Basic PDU

Engineered to distribute UPS, generator or utility AC power to equipment.

The CyberPower 8-outlet (8 Rear) rack mount basic power distribution unit (PDU30BHVT8R) provides 208V/230V 30A output. It distributes power to 8 IEC-320 (2-C19/6-C13) receptacles from a single NEMA L6-30P twist lock plug, with unfiltered electrical pass-through.

Designed for datacenters and other electrically demanding applications, this unit has a rugged, industrial-grade metal housing and a 10-foot AC power cord. It supports vertical, horizontal and wall mount installation, includes a cord retention tray and is ETL/ROHS certified.

A Lifetime Warranty ensures that this PDU is free of defects in design, assembly, material and workmanship.

Typical Applications

- Servers
- Network Devices
- Telecom Equipment

Features

- Basic PDU
- Switch-Free Design
- Industrial-Grade Metal Housing
- Lifetime Warranty

PDU30BHVT8R Basic PDU

Engineered to distribute UPS, generator or utility AC power to equipment.

GENERAL	
Туре	Basic PDU
Phase	Single Phase
INPUT	
Voltage	200V / 230V
Current	30A max (derated to 24A)
Frequency	50Hz/60Hz
Plug Type	NEMA L6-30P
Plug Style	Straight, Twist Lock
Cord Length	10'
OUTPUT	
Nominal Output Voltage	200V/230V
Outlets - Total	8
Outlet Type	IEC-320 C19/C13
Outlets - Front	0
Outlets - Rear	2(C19)+6(C13)
LED Indicators	Bank 1 Green – Bank 2 Green
Overload Protection	16A x 2
PHYSICAL	
Rack Size	OU
Form Factors Supported	Vertical Rackmount, Wallmount
Cord Retention Organizers	Yes
External Site Ground Pin	Yes
Adjustable Mounting Brackets	2 sets (L-short, L-long)
Dimensions (WxHxD) (in.)	17.5 x 1.75 x 1.5
Weight (lbs.)	4.5
ENVIRONMENTAL	
Operating Temperature	32°F to 95°F / 0°C to 35°C
Operating Relative Humidity	0% - 95% non-condensing
Storage Temperature	5°F to 113°F / -15°C to 45°C
Maximum Operating Elevation	10,000 ft / 3,000 m
Maximum Storage Elevation	50,000 ft / 15,000 m
CERTIFICATIONS	
Safety	UL60950_1 certified by ETL (USA), CSA C22.2 (Canada)
Environmental	RoHS Compliant
WARRANTY	
Product Warranty	Lifetime