

## 10U 19in Wall Mounted Server Rack Cabinet

StarTech ID: CAB1019WALL



The CAB1019WALL 10U Wall Mounted Server Rack Cabinet can be mounted to most wall materials, allowing you to securely position your rackmount equipment exactly as needed. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The server rack offers 10U of storage space and is designed to accommodate standard 19in (wide) rack equipment. To ensure a cool operating environment for your equipment, the server rack includes a 5in roof-mounted fan (85 CFM) and vented side panels - not only helping to keep temperatures down, but keep dust out of the rack.

To secure network and server equipment from tampering, the cabinet features a lockable, smoked acrylic front door, that can be removed entirely or installed to open from the left or right as needed.

Backed by a StarTech.com Lifetime warranty and free lifetime technical support.

### Applications

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore location
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization
- Mount Audio/Video broadcast or distribution components

## Features

- Fully adjustable mounting rails inside cabinet
- Front door is removable and can be switched to open left or right
- TAA compliant for GSA Schedule purchases
- Includes one, roof-mounted 5" (12cm) fan for up to 85 CFM of airflow
- Ships fully assembled and ready to use
- Includes a lockable & removable smoked acrylic front door with 2 keys
- Stylish enclosure is designed for durability and easy accessibility

## Technical Specifications

Warranty	Lifetime
Fan(s)	Yes
Fans	1 - 5in
Frame Type	Enclosed Cabinet
Front Door Type	Steel w/ Window
Industry Standards	EIA RS310-C
Key Lock	Yes
Rack Type	2-Post
U Height	10U
Wallmountable	Yes
Air Flow Rate	85 CFM
Noise Level	36 dBA
Weight Capacity	132.6 lb [60 kg]
Input Current	180 mA
Input Voltage	115 AC
Color	Beige
External Depth	23.6 in [600 mm]
External Height	20 in [508 mm]
External Width	22 in [560 mm]
Internal Depth	22.7 in [576.6 mm]
Internal Height	17.6 in [448 mm]
Internal Width	18.3 in [465 mm]
Maximum Mounting Depth	17.7 in [450.9 mm]
Product Weight	48.6 lb [22 kg]
Flat Pack	No
Shipping (Package) Weight	51.2 lb [23.2 kg]
Included in Package	1 - 10U Server Rack Cabinet
Included in Package	20 - M5 Screws
Included in Package	20 - M5 Cage Nuts
Included in Package	4 - Wall Anchor
Included in Package	4 - Lag Screws
Included in Package	2 - Keys
Included in Package	1 - Instruction Manual

## Certifications, Reports and Compatibility



**RoHS Compliant**  
Available