

Adjustable Rackmount DIN Rail Kit with Top Hat/Mini/G Rails

StarTech ID: ADJDINKIT



The ADJDINKIT Adjustable Rack Mount DIN Rail Kit with Top Hat/Mini/G Rails makes mounting your DIN-rail equipment in a 19-inch server rack/cabinet or wall plate simple, without wasting space due to special bracket requirements for each piece of equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This 19-inch DIN Rail Mounting Kit includes the three most commonly used DIN rail systems: Top-Hat, Miniature Top-Hat, and G-Type.

Backed by a StarTech.com Lifetime Warranty.

Applications

- Install DIN Rail mountable hardware into a standard 19" rack or cabinet
- Two ADJDINKIT's can be used in the same U height, facing each other and mounted on both front and back rails

Features

- Includes three types of DIN rails: Top-Hat, Miniature Top-Hat, and G-Type
- Fits all standard 19" racks
- TAA compliant for GSA Schedule purchases
- Meets ANSI/EIA RS-310-D standards
- Occupies 2U of rack space
- Adjustable depth
- Constructed from solid cold press steel

Technical Specifications

Warranty	Lifetime
Frame Type	Steel
U Height	2U
Color	Black
External Depth	14.1 in [358.4 mm]
External Height	3.5 in [88.9 mm]
External Width	19 in [482.6 mm]
Internal Depth	8.7 in [222.3 mm]
Internal Height	3.3 in [85 mm]
Internal Width	16.4 in [416.8 mm]
Maximum Mounting Depth	8.7 in [222.3 mm]
Product Weight	3.8 lb [1.7 kg]
Shipping (Package) Weight	92.1 oz [2610 g]
Included in Package	1 - Din Rail mounting brackets
Included in Package	1 - G-Type Top-Hat Din Rail
Included in Package	1 - Miniature Top-Hat Din Rail
Included in Package	1 - Top-Hat Din Rail
Included in Package	1 - Package of M5 screws and nuts (4 each)
Included in Package	2 - Carriage Bolts
Included in Package	2 - DIN rail mounting Screws
Included in Package	2 - Wing Nuts
Included in Package	4 - Plastic Washers

Certifications, Reports and Compatibility



RoHS Compliant
Available