


2 Port VGA Video Splitter with Audio - USB Powered

StarTech ID: ST122LEA



Our most compact two port VGA and audio splitter with USB bus power to reduce clutter

This 2 Port VGA Video Splitter with Audio and USB power is our most compact VGA splitter, allowing a computer to simultaneously display VGA video on two monitors from a single source.

Perfect for classrooms, tradeshow, or any environment requiring high quality video on several monitors, the ST122LEA VGA splitter supports displays with up to 2048x1536 resolution and stereo audio.

Plus, to simplify placement of this VGA splitter, it can use power from a PC or media player with a USB port, without having to use a conventional power adapter. The splitter features a built-in booster circuit that allows you to locate VGA monitors up to 200ft away from your system.

The ST122LE VGA Splitter supports easy plug and play installation, and is backed by StarTech.com's 1-year warranty and FREE lifetime tech support.

Applications and Solutions

-
-

-
-
- Ideal for small digital signage installations with little space or power outlets. Simply plug into a USB port.
- Some applications where the ST122LEA can be used in include; education, POS (retail), hospitality, healthcare, and houses of worship.

Features

- Compact, space-saving design
- Includes USB power cord
- Provides brilliant resolutions up to 2048 x 1536 60 Hz
- 300 MHz bandwidth for high bandwidth fast moving video
- Supports stereo audio using 3.5mm audio jacks
- Maximum distances up to 65 meters (213 feet)

Technical Specifications

- Warranty: 1 Year warranty
- Color: Black
- Connector Types: 2 - DB15 Female
- Connector Types: 1 - DB15 Male
- Connector Types: 3 - Phono 3.5 mm Female
- Enclosure Type: Plastic
- Product Height: 0.91 in [23 mm]
- Input Current: Bandwidth: 300MHz
- Product Length: 2.68 in [68 mm]
- Maximum Analog Resolutions: 2048x1536
- Number of Ports: 2
- Product Weight: 4.06 oz [115 g]
- Product Width: 2.09 in [53 mm]
- DDC Support: DDC, DDC2, DDC2B, on Video Out Port 1
- Max Distance: 65m / 210ft
- Power Adapter: DC 5V 500mA - USB Powered
- Audio Support: Yes (3.5mm Stereo)
- LED Indicators: 1 - Green - Power
- Wide Screen Supported:: Yes
- Humidity: 0~95% RH
- Operating Temperature: 0°C to 70°C (32°C to 158°C)
- Storage Temperature: -20°C to 85°C (-4°C to 185°C)
- Shipping (Package) Weight: 0.4 lb [0.18 kg]

- Carton Quantity: 40

