

# Konftel 250

The nice thing about conference calls



The Konftel 250 is an excellent choice when you want to hold standard telephone conferences without compromising on sound quality. Simply make the call and get straight down to business. No need for you, your colleagues and your partners to waste time on complicated setups.

The Konftel 250 fits everything from small huddle rooms to large conference rooms. It includes the option to connect a pair of expansion microphones to increase the pickup range and cover up to 20 people in a room. The phone is equipped with Konftel's OmniSound® for crystal-clear sound in both directions.

## OmniSound®

- Meeting size: Up to 20 people
- Analog
- OmniSound® with HD audio
- Expandable with additional microphones
- Recording on memory card
- Guide for multi-party calls
- Two-year warranty



### SMART FEATURES

Save contacts in the phone book. The conference guide will take you through the steps to set up a multi-party call and create call groups. Record important calls on an SD memory card, as back-up for notes or to share at a later date.



### SCANDINAVIAN DESIGN

The audio is expertly designed around our OmniSound® technology, which comes as standard in all our products. The style of the Konftel 250 is anything but standard, allowing it to take pride of place in the finest conference rooms. The classic Scandinavian design is both visually appealing and functional.

## Specifications Konftel 250

### GENERAL

**Product name:** Konftel 250

**Item number:** 910101065

**Contents:** Konftel 250, phone line/power connection cable (900103385) and AC adapter (900102125).

**Product documentation:** Manual and Quick Reference Guide available online in Danish, Dutch, English, Finnish, French, German, Italian, Norwegian, Polish, Russian, Spanish, Swedish and Turkish.

**Warranty:** 2 years.

**Size:** Diameter 240 mm, height 77 mm

**Weight:** 1 kg.

**Color:** Charcoal black.

**Anti-theft protection:** Kensington security slot.

### USER INTERFACE

**Display:** Backlit monochrome LCD, 128x64 pixels.

**Keypad:** Alphanumeric 0-9, \*, call/R, end call, mute, hold, volume up, volume down, 5 buttons for menu navigation, phone book, conference guide

**Menu languages:** Danish, Dutch, English, Finnish, French, German, Italian, Norwegian, Polish, Russian, Spanish, Swedish, Turkish.

**Phone book:** 50 contacts.

**Conference guide:** Stores up to 20 call groups. Support for multi-party calls.

### CALL FEATURES

**During calls:** Put calls on hold. Call waiting. Park/retrieve calls (if supported by PBX). Move incoming calls. Request. Music on hold. Dial plan.

**Multi-party calls:** Support for multi-party calls if supported by exchange.

### POWER SUPPLY

**AC adapter:** 100-240 V AC/14 V DC.

### CONNECTIVITY

**Analog:** 6/6 modular (RJ11) to a public analog telecommunication network or an analog PBX.

### APPROVALS

**Security:** EN 60950-1:2006/A1:2010. EN 60950-1:2006/A12:2011. EN 60950-1:2006/A2:2013. IEC 60950-1:2005/A1:2009.

**EMC:** EN 55022 (2010). EN 55024 (2010). EN 61000-3-2:2006+A1+A2. EN 61000-3-3:2013.

**Tele:** TBR21:1998.

### CONNECTION TO DEVICES

**Expansion microphones:** 2 x modular 4/4.

### AUDIO SPECIFICATIONS

**Technology:** OmniSound®

**Microphone:** Omnidirectional 360°.

**Reception area:** Up to 12 people (30 m<sup>2</sup>), with expansion microphones up to 20 people (70 m<sup>2</sup>).

**Speakers:** Frequency band 200-3300 Hz.

**Volume:** Max 90 dB SPL 0.5 m.

**Equalizer:** Dark, neutral, bright.

### ADDITIONAL FEATURES

**Recording:** Support for SD/SDHC (≤32 GB) memory card from software version 1.19.184.

### ENVIRONMENT

**Temperature:** 5° - 40°C.

**Relative humidity:** 20 - 80% condensation-free.

## Related products and accessories



### KONFTEL 300

Konftel 300 with OmniSound® for superb audio quality. Smart features such as re-recording, conference guide and line selector (analog/cell/USB for VoIP). Add expansion microphones for meetings of over 12 people and a wireless headset or connect to the PA system for very large meetings. Future-proof, can be updated.

**Item number:** 910101059



### KONFTEL 300Wx

The Konftel 300Wx wireless conference phone allows you to hold meetings wherever is convenient for you - without worrying about network and power outlets. Choose a base station to suit your company's telephony environment, SIP or analog, or connect to an installed DECT system. The rechargeable battery gives you up to 60 hours of call time.

**Item number:** 910101078/840101078



### EXPANSION MICROPHONES

1 pair. Increase the voice pickup range from 30 up to 70 m<sup>2</sup>. Two lengths of cable supplied, 1.5 and 2.5 m.

**Item number:** 900102113

RETAILER SPACE

© Konftel AB. In line with our policy for continuous product development, we reserve the right to change the product specifications. Visit [www.konftel.com](http://www.konftel.com) for the latest information.

Konftel is a leading company within collaboration endpoint solutions. Since 1988, our mission has been to help people in businesses around the world to have meetings regardless of distance. Based on our success, we know that remote collaboration is a smooth way to save time, money and at the same time contribute to a more sustainable world. Crystal clear audio and a sharp video image are essential for efficient meetings, this is why we only focus on cutting-edge technology in our Collaboration Solutions. Our audio technology OmniSound® is built into all Konftel Conference phones and devices. The products are sold globally under the Konftel brand and our headquarter is based in Sweden. Read more about the company and our products at [konftel.com](http://konftel.com).