

## 4 Port DVI Video Splitter with Audio

StarTech ID: ST124DVIA



### Split a DVI and Audio signal to four displays with support for HD resolutions

The ST124DVIA DVI splitter lets you share one DVI video and audio source on four displays and acts as a signal amplifier that allows you to locate your DVI monitors up to 33ft (10 m) away from your computer or DVI signal source.

With support for high definition resolutions up to 1080p (HDTV)/1920x1200 (PC), the DVI splitter delivers a simple and convenient DVI video solution that suits virtually any application or operating environment (classroom, healthcare, professional A/V, control centres, retail POS environments).

The DVI video splitter/distribution amplifier is easy to install, providing you with flawless digital video that will help you get the most from your DVI-enabled monitors, projectors, or plasma screens.

Designed to provide dependable performance, the DVI splitter/signal distribution amplifier is backed by StarTech.com's 1-year warranty and FREE lifetime tech support.

### Applications and Solutions

- Connect DVI projectors, monitors, large displays, and wall display systems for digital signage applications and ensuring content is delivered to target audience.

- Great for use in tradeshows, POS retail, healthcare, transportation terminals, education, house of worship.

## Features

- Supports resolutions of up to 1920 x 1200 pixels @ 60 Hz
- Split both video and 3.5mm analog stereo audio
- DVI, and HDCP compliant for easier HD video distribution
- Easy setup for a quick connection in minutes
- Accurate and reliable reproduction of digital video signal, with no signal attenuation or distortion

## Technical Specifications

- Warranty: 1 Year warranty
- Color: Black
- Product Height: 1.73 in [44 mm]
- Product Length: 8.66 in [220 mm]
- Number of Ports: 4
- Product Weight: 38.83 oz [1100 g]
- Product Width: 5.31 in [135 mm]
- Enclosure Type: Aluminum
- LED Indicators: 1 - Green - Power/Link
- LED Indicators: 4 - Green - Link
- Maximum Digital Resolutions: 1920 x 1200 @ 60Hz
- Wide Screen Supported:: Yes
- Output Signal: DVI-D (DVI Digital)
- Connector A: 1 - 29 pin DVI-I (Dual Link) Female
- Connector A: 1 - 3.5 mm Stereo Female
- Connector B: 4 - 29 pin DVI-I (Dual Link) Female
- Connector B: 4 - 3.5 mm Stereo Female
- Power Adapter Included: Yes
- Output Voltage: 9 DC
- Output Current: 600mA
- Center Tip Polarity: Positive
- Technical Standards: DVI 1.0, and HDCP 1.1
- Humidity: 0~80% RH
- Operating Temperature: 0°C to 40°C (32°F to 104°F)

- Storage Temperature: -20°C to 60°C (-4°F to 140°F)
- Shipping (Package) Weight: 4.64 lb [2.1 kg]
- Carton Quantity: 6

