

Long Range USB VGA KVM Console Extender over Cat5 UTP - 1000 ft

StarTech ID: SV565UTPUL



This long range USB VGA KVM Console Extender lets you control a server, computer or multiple computers (connected through KVM Switch) over a standard Cat5 or Cat6 UTP network cable connection, at distances of up to 1000ft away.

You can use your existing USB keyboard, USB mouse, and monitor to access both the server room and your office computer, saving space and avoiding the need for a dedicated remote console by allowing you to switch between workstation view and KVM view at the remote location.

Designed to provide long lasting, reliable operation, the SV565UTPUL USB VGA Long Range KVM Console Extender is backed by StarTech.com's three year warranty.

Applications and Solutions

- Allow two users to share one PC or KVM
- Control remote machines and security monitoring systems
- Monitor computer-controlled equipment in a factory or warehouse at a distance
- Use one or more servers in a server room from a remote location

Features

- High resolution support: Up to 1920x1200(WUXGA)/ 1600x1200(UXGA)
- Kit includes both local and remote units
- Compatibility mode enables hotkey commands to be passed to connected StarView KVMs
- USB computers are supported at the host and remote locations (USB keyboard and mouse required for remote console)
- Supports auto-switching between host and remote users or dedicated control
- Supports most combo keyboard and mouse sets (including Wireless)
- Compatible with CAT 5, 5e, or 6 UTP cabling
- Hotkey controlled Equalizer(sharpness), Gain(brightness), and RGB Skew adjustments
- Intuitive hotkey commands

Technical Specifications

- Warranty: 3 Year warranty
- Color: Black
- Power Adapter - Amperage: .6
- Power Adapter - DC Voltage: 9 (DC)
- Enclosure Type: Steel
- Supported Platforms: USB
- Maximum Analog Resolutions: UXGA - 1600x1200, WUXGA - 1920x1200
- Wide Screen Supported: Yes
- LED Indicators: 2 - Remote indicator
- LED Indicators: 2 - Local indicator
- Port Selection Support: Push Button and Hotkeys
- Cables Included: Yes
- Maximum Cable Length: 300m (984 ft)
- Console Interface(s): 2 - High Density DB15 (VGA) Female
- Console Interface(s): 4 - USB A Female
- Host Interface(s): 2 - High Density DB15 (VGA) Female
- Other Interfaces: 2 - RJ45 Female
- Power Adapter Included: Yes
- Input Voltage: 115 AC
- Output Voltage: 9 DC

- Output Current: 600mA
- Center Tip Polarity: Positive
- Product Height: 0.79 in [20 mm]
- Plug Type: M
- Product Weight: 52.95 oz [1500 g]
- Product Width: 6.18 in [157 mm]
- Product Depth: 2.76 in [70 mm]
- Humidity: 0~80% RH
- Operating Temperature: 0°C to 40°C (32°F to 104°F)
- Storage Temperature: -20°C to 60°C (-4°F to 140°F)
- Shipping (Package) Weight: 88.25 oz [2500 g]
- Carton Quantity: 6

