

HI-FIDELITY PC MICROPHONE HEADSET

- ANDREA NOISE CANCELLATION MICROPHONE TECHNOLOGY WITH HIGHEST VOICE RECOGNITION INDUSTRY RATING
- PRO-FLEX WIRE MICROPHONE BOOM FOR ACCURATE MICROPHONE PLACEMENT
- 40MM SPEAKER WITH CD QUALITY SOUND AND LARGE COMFORTABLE EARCUSHION
- IN-LINE VOLUME AND MUTE CONTROLS
- STAINLESS STEEL ADJUSTABLE HEADBAND
- WINDSOCK FOR MINIMAL BREATH POPPING
- REVERSIBLE FOR LEFT OR RIGHT SIDE USAGE
- FOLDS FLAT FOR STORAGE AND PORTABILITY
- EXTRA LONG 8 FOOT SHIELDED CABLE



Parameter	Value
Connections	
Microphone Plug 3.5mm	Pink (PMS 701C)
Speaker Plug 3.5mm	Green (PMS 365C)
Microphone	
Noise Cancellation	5 dB/octave
Frequency Range	100-10,000 Hz
Electrical Signal-to-Noise Ratio	>60 dB
Sensitivity at 1 kHz (0 dB = 1 V/Pa)	-44 dB
Current Consumption	<0.5 mA
Headphone Speaker	
Frequency Range	50-20,000 Hz
Coil Resistance	32 ohm
Sound Output from 1 kHz 1mW Input (0 dB = 20 μ Pa)	114 dB
Max. Input Power	40 mW