

Description

Specifications -

Altronix ReServ1 Video Surveillance UPS is designed to simultaneously provide power for 24VAC and 12VDC cameras during normal or power outage conditions. True sine wave regulated AC outputs and regulated DC outputs.



Altronix®

ReServ1 (order batteries separately)

| - Specifications | | | |
|--|--|--|---|
| Input | | Indicators (Audio and LED) | |
| Voltage | 115VAC, 60Hz, 3.5A. | Input | Input voltage is present. |
| | | DC Output | Powered. |
| Outputs | | Outputs | Individual Indicators. |
| 16 individual PTC protected power-limited auto-resettable outputs rated 1A each. | | Audio | AC Fail and Battery Fail. |
| Voltage | Twelve (12) outputs @ 24VAC. | Agency Listings | |
| _ | Four (4) outputs @ 12VDC. | UL/cUL | UL60950-1 (Information Technology). |
| Current | 24VAC @ 4A (0.33A per device, 1A max.) and 12VDC @ 2A (0.5A per device, 1A max.). | CE | European Conformity. |
| | (Ambient Temperature -33°C to 30°C). 24VAC @ 3.5A (0.29A per device, 1A max.) and 12VDC @ 2A (0.5A per device, 1A max.). (Ambient Temperature -33° to 42° C). Short circuit and thermal overload protection. | Physical and Environmental | |
| | | Dimensions (H x W x D) | |
| | | 13.5" x 13" x 3.25" (342.9mm x 330.2mm x 82.55mm). | |
| Other | | | odates up to two (2) 12VDC/7AH batteries. |
| | | Product Weight | |
| Back-up Battery (not included) | | Shipping Weight | 11.26 lbs. (5.11 kg). |
| Туре | Sealed lead acid or gel type. | Temperature | |
| Failover | Upon AC loss, instantaneous. | Storage | -20°C to 70°C (-4°F to 158°F). |
| | | Relative Humidity | / 85% +/-5%. |
| Supervision | | BTU/Hr. (approx.) |): 61 BTU/Hr. |
| AC Failure | Form "C" contacts. | | |
| Low Battery | Form "C" contacts. | | |
| | | | |

