

LG M4214C

42" 16:9 LCD Display



LCD WIDESCREEN FULL HD MONITOR

- Full HD 1920*1080
- 3 year limited warranty
- eZ-Net manager
- PC Built-in Ready (NC2000 Compatible)
- USB Playback
- RoHS compliant
- Energy Star 5.0
- ErP Certified



LG Commercial Display

LG M4214C

42" 16:9 LCD Display



LG Electronics
www.lgcommercial.eu
www.lge.com



PANEL

SCREEN SIZE	42"
ASPECT RATIO	16:9
NATIVE RESOLUTION	1920*1080 (FHD)
PIXELS (HXVX3)	6,220,800
BRIGHTNESS	500CD/M2
CONTRAST RATIO	1,300:1, 40,000:1 (DCR)
VIEWING ANGLE (HXV)	178X178
COLOR DEPT	1.06 BILLION
RESPONSE TIME	10MS (G TO G)
LIFE TIME	50,000 HR. PORTRAIT & LANDSCAPE

VIDEO (PC)

MAX INPUT RESOLUTION	1920 X 1080@ 60HZ(RGB, HDMI/DVI)
RECOMMENDED RESOLUTION	1920 X1080@ 60HZ(RGB, HDMI/DVI)
H-SCANNING FREQUENCY	30 ~ 83KHZ(RGB, HDMI/DVI)
V-SCANNING FREQUENCY	56 ~ 75HZ (RGB), 60HZ(HDMI/DVI)
VIDEO INPUT	RGB, HDMI, DVI

REAR INPUTS

COMPONENT VIDEO	1HI-RES
PC INPUT VIA 15-PIN SUB "D"	YES 1 / 1
COMPOSITE VIDEO	YES, 1 HI-RES
AUDIO OUTPUT	YES
AUDIO INPUTS	YES, 2 PLUS PC SOUND
HDMI/DVI WITH HDCP	YES
RJ-45	YES
EXTERNAL SPEAKEROUT	YES

AUDIO


AUDIO POWER	20W (10WX2)
COMMON SPEAKER	YES
SPEAKER ON/OFF	YES

SPECIAL FEATURES

NEW TEMPERATURE SENSOR	YES
VIDEO WALL, MAX 5X5	YES
DISPLAY CONTROL	SINGLE/GROUP WAN CONTROL, SCHEDULING, INSTANT MESSAGING, SELF DIAGNOSIS (TEMP, FAN, LAMP, POWER DETECT) ALARM SERVICE THOURGH MAILING. EASY TILE MODE SETUP. S/W UPGRADE VIA NETWORK, USB PLAYBACK
BRIGHTNESS / CONTRAST	YES
ISM METHOD	NORMAL/WHITE WASH/ORIBTER/INVERSION
INFORMATION DISPLAY	SERIAL NUMBER, MNT S/W VERSION, LAN S/W VERSION, IP ADDRESS, MAC ADDRESS

CABINET

MONITOR DIMENSION (WXHxD)



WEIGHT (HEAD+STAND+SPEAKER)	23,74KG
VESA STANDARD MOUNT INTER-FACE	600X400 (APWX60)

POWER

POWER SUPPLY	100-240V~, 50/60HZ
POWER TYPE	BUILT-IN POWER
POWER SWITCH TYPE	YES
POWERSAVING	
NORMAL	200W
DPMS OFF	1W(RGB), 2W(HDMI)
SWITCH OFF	0.5W

INTERFACE



2011 Disclaimer: Design, features and specifications are subject to change without notice.