

## AEC Models

# Adjustable Extension Column

For various flat panel mounts, projector mounts and ceiling plate accessories

Designed to blend in and work with almost any environment, our line of nine AEC adjustable columns range in lengths from 6-9" up to 10-12', and many lengths in between. Whether it's for an office or mounted from a tall cathedral ceiling, the adjustable column supports up to 900lb, making it ideal for exhibit, retail or digital signage applications. The new slot design makes for easy incremental height adjustments to find the perfect position and then securely locking it into place. The AEC column's cylinder shape conveniently offers ample internal space for cable management of multiple cords, ultimately giving a clean look to any installation.



Max load: 900lb (408kg)

### FEATURES

- 1-1/2"-11.5 NPT (38mm) schedule 40 pipe threaded on both ends
- Height adjustment at 1" (25mm) increments
- Made of steel for use with multiple screen applications
- Offers unobtrusive cable management
- Notched adjustment design enables easy height adjustment and position locking
- Available in black, white and silver to match flat panel screens, projectors, mounts and ceiling surfaces
- 900lb load capacity



- **EASE OF ADJUSTABILITY**  
Simplest slot design allows for easy glide adjustment



Available in black, white and silver to match flat panel screens, projectors and ceiling mount surfaces

**AEC Models:** Adjustable Extension Column for various flat panel mounts, projector mounts and ceiling plate accessories


**Product Specifications**

	DIMENSIONS (COLUMN LENGTH)		PRODUCT WEIGHT		LOAD CAPACITY	FINISH	AVAILABLE COLORS
AEC006009(-S)(-W)	6" - 9"	(.15 - .23m)	1.94lb	(.88kg)	900lb (408kg)	Scratch resistance fused epoxy	AEC006009 - AEC1012: Black
AEC012018(-S)(-W)	12" - 18"	(.30 - .46m)	3.64lb	(1.65kg)			AEC006009-S - AEC1012-S: Silver
AEC018024(-S)(-W)	18" - 24"	(.46 - .61m)	7lb	(3.17kg)			AEC006009-W - AEC1012-W: White
AEC0203(-S)(-W)	2' - 3'	(.61-.91m)	9.1lb	(4.12kg)			
AEC0305(-S)(-W)	3' - 5'	(.91 - 1.52m)	14lb	(6.35kg)			
AEC0406(-S)(-W)	4' - 6'	(1.22 - 1.83m)	16.6lb	(7.53kg)			
AEC0608(-S)(-W)	6' - 8'	(1.83 - 2.44m)	23lb	(10.43kg)			
AEC0810(-S)(-W)	8' - 10'	(2.44 - 3.05m)	27.6lb	(12.52kg)			
AEC1012(-S)(-W)	10' - 12'	(3.05 - 3.66m)	34lb	(15.42kg)			


**Package Specifications**

	PACKAGE SIZE (L x H x W)	PACKAGE SHIP WEIGHT	PACKAGE UPC CODE	PACKAGE CONTENTS	UNITS IN PACKAGE
AEC006009(-S)(-W)	9.5" x 2.5" x 2.5" (241.3 x 63.5 x 63.5mm)	2.16lb (.98kg)	AEC006009: 735029275121 AEC012018: 735029275159 AEC018024: 735029275183 AEC0203: 735029267027 AEC0305: 735029267034 AEC0406: 735029267041 AEC0608: 735029267058 AEC0810: 735029267065 AEC1012: 735029267072	Extension pipe, adjuster tube and M8 x 10 mm screw	1
AEC012018(-S)(-W)	14" x 2.5" x 2.5" (355.6 x 63.5" x 63.5mm)	3.98lb (1.80kg)	AEC006009-W: 735029275145 AEC012018-W: 735029275176 AEC018024-W: 735029275206 AEC0203-W: 735029267126 AEC0305-W: 735029267133 AEC0406-W: 735029267140 AEC0608-W: 735029267157 AEC0810-W: 735029267164 AEC1012-W: 735029267171		
AEC018024(-S)(-W)	21" x 2.5" x 2.5" (533.4 x 63.5 x 63.5mm)	5.72lb (2.59kg)	AEC006009-S: 735029275138 AEC012018-S: 735029275169 AEC018024-S: 735029275190 AEC0203-S: 735029267218 AEC0305-S: 735029267225 AEC0406-S: 735029267232 AEC0608-S: 735029267249 AEC0810-S: 735029267256 AEC1012-S: 735029267263		
AEC0203(-S)(-W)	27" x 2.5" x 2.5" (685.8 x 63.5 x 63.5mm)	7.87lb (3.57kg)			
AEC0305(-S)(-W)	39" x 2.5" x 2.5" (990.6 x 63.5 x 63.5mm)	13.01lb (5.90kg)			
AEC0406(-S)(-W)	47" x 2.5" x 2.5" (1193.8 x 63.5 x 63.5mm)	16.53lb (7.49kg)			
AEC0608(-S)(-W)	71" x 2.5" x 2.5" (1803.4 x 63.5 x 63.5mm)	22.47lb (10.19kg)			
AEC0810(-S)(-W)	95" x 2.5" x 2.5" (2413 x 63.5 x 63.5mm)	28.42lb (12.89kg)			
AEC1012(-S)(-W)	119" x 2.5" x 2.5" (3022.6 x 63.5 x 63.5mm)	34.25lb (15.53kg)			

All dimensions = inch (mm)



Height Adjustment	
MODEL	"X"
AEC006009	6" - 9" (152 - 229mm)
AEC012018	12" - 18" (305 - 457mm)
AEC018024	18" - 24" (457 - 610mm)
AEC0203	24" - 36" (610 - 914mm)
AEC0305	36" - 60" (914 - 1524mm)
AEC0406	48" - 72" (1219 - 1829mm)
AEC0608	72" - 96" (1829 - 2438mm)
AEC0810	96" - 120" (2438 - 3048mm)
AEC1012	120" - 144" (3048 - 3656mm)



**ARCHITECTS SPECIFICATIONS**

The Adjustable Extension Column shall be a Peerless model AEC006009, AEC012018, AEC018024, AEC0203, AEC0305, AEC0406, AEC0608, AEC0810 or AEC1012 and shall be located where indicated on the plans. The finish shall be scratch resistant black, silver or white. Assembly and installation shall be done according to instructions provided by the manufacturer.