



A6 Duplex Scanner

Scanshell® 800DXN is a high-speed A6 duplex card scanner which offers simultaneous high image quality capture of both sides of the scanned document.

Scanshell® 800DXN is equipped with high speed USB 2.0 standard interface and requires no external power supply.

With its light weight, small footprint and simple connection, the **Scanshell® 800DXN** is a unique and convenient solution for simultaneous double side scanning for both desktop and mobile use.

Scanner Specification

- **Interface:** USB 2.0 (Universal Serial Bus) High speed
- **Image sensor:** Dual, linear color CMOS CIS
- **Optical Resolution:** 600 dpi x 1200 dpi
- **Power Consumption:** 0.2W Stand-by, 2.0W during Scanning
- **Scanning Area:** Cards and documents up to 4.25"(10.6cm)x 7.25" (18.4cm)
- **Scan Speed (100dpi):** 12 pages per minute B&W
6 pages per minutes Color
- **Scan Modes:** internal 48bit, outputs 24bit color, 8bit grey, 1bit black & white.
- **Media Thickness:** 0.1mm- 1.5mm
- **Paper Sensor:** Electro- mechanical
- **Safety Standards:** FCC class B, CE

Features

- USB 2.0 interface, no external power required
- Light-weight and fully portable
- Small footprint
- **Twain** compatible

Dimensions

- L x W x H: 8" x 2.75" x 1.8"
- Weight: 16.9oz (480g)

System Requirements

- Windows 2000, XP & Vista