

Give your business a big advantage with professional colour output. This laser multifunction offers powerful SEND functionality and auto duplexing in a robust, easy to use unit.

Workhorse Plus

This multifunction will allow you to benefit from superior colour printing, faxing, copying and scanning in one stylish, cost cutting and space saving unit. It allows you to give your marketing materials added impact with beautiful colour images, bold graphics and sharp text.

The imageCLASS MF9220Cdn allows you to scan your documents quickly and easily for direct distribution via email, network file server, FTP server, internet fax or USB key.

The 3.5 inch colour TFT display with easy-scroll wheel allows easy access to all the features.



Key Features

All-in-One cartridges Toner Cartridges

- The MF9220Cdn utilises a drum cartridge in which an "Intermediate Transfer Unit", "Photosensitive Drum", and "Waste Toner Container" that are normally individual consumables, are all combined, meaning less consumables to stock and less fuss.

Low Power Consumption and Quick Start Up

- By adopting Canon's unique On-Demand Fixing System, there is zero warm up time, so no waiting. The unit springs into action the moment it's needed and with up to 21ppm colour print or copy speeds. The MF9220Cdn is also energy star certified and consumes only 1.2 watts of power in sleep mode, so you not only save on your electricity bill but also the environment too.

As a Laser Printer

- Up to 21 pages per minute for colour and mono with 16 seconds to first print
- 600 x 600 dpi laser print resolution (enhanced to 2400 x 600 dpi by smoothing technology).
- 384MB Memory
- Auto duplex for easy double sided printing and copying
- 3.5" colour TFT display with easy scroll wheel giving you access to all functions.

As a Fax Machine

- 33.6 Kbps Super G3 fax - up to 3 seconds per page³ fax transmission.
- Huge fax memory of up to 1000 pages³ to ensure there are no lost messages.
- 50-page Automatic Document Feeder for fast, unattended copying and faxing.

As a Scanner

- Up to 600 x 1200 dpi (optical) and 9600 x 9600 dpi (interpolated) colour scanning resolution for sharp images

As a Copier



Quality images

High print resolution (21 ppm, 600 x 600 dpi / up to 1200 x 600 dpi enhanced) @ 21 ppm



High Quality Copying

Laser copy quality 600 x 600 dpi @ 21 cpm



Auto duplex for copy & print

Auto duplex for easy double sided printing and copying



Integrated Network

Integrated network for workgroup printing



50-page Automatic Document Feeder (ADF) for fast unattended copying and faxing.

Fax Memory

Huge fax memory of up to 1000 pages to ensure there are no lost messages



Quality Scanning

CCD scanning at 600 x 1200 dpi (optical) and 9600 x 9600 dpi (interpolated)



Easy Maintenance

All-in-one cartridge system meaning only 1 consumable to stock

Toner Gauge

Useful toner gauge function to confirm remaining toner quantity

Laser Printers

Canon laser printers combine a range of features and technologies to deliver fast, high quality and reliable printing. So, if you are looking to create professional business documents while reducing your running costs, Canon lasers fit the bill.

Model	MF9220Cdn
Copy Type	Colour Laser
Copy Speed	Black/Colour : 21/21cpm (A4), 22/22cpm (letter)
Copy Resolution	600 x 600 dpi
Halftones	256 Levels
Warm up Time	Less than 60 sec
First Copy Time	Approx. 12.5sec/12.5sec (Black/Colour)
First Print Time	
Paper Source(s)	250-sheet cassette plus 100-sheet multipurpose tray
Optional Cassette	Optional 500-sheet cassette pedestal
Paper Weight	60 to 120 g/m2(cassette), 60 to 176g/m2(multipurpose tray)
Paper Output	250 sheets (face down)
Duplex Copy / Bind Type	Yes, 1 to 2, 2 to 1, 2 to 2 /Book, Calender
Reduce/Enlargement	50%, 70%, 81%, 86% / 115%, 122%, 141%, 200% (AB system)
Zoom	50 - 200% in 1% increments
Document Feeder	50-Sheet (*1)
Copy Size	ADF: 5.5" x 5" to 8.5" x 14" / 139.7 x 128mm to 215.9 x 355.6mm
Copy Features	ACS(Auto Colour Select), Frame Erase, Memory Sort, Toner Save, 2 on 1, 4 on 1
Copy Memory	384MB (Shared)
Printer Specification	
Printer Type	Colour Laser
Print Speed	Black/Colour : 21/21cpm (A4), 22/22cpm (letter)
Print Language	UFR II LT (Host Based)
Print Resolution	600 x 600 dpi, 2400 x 600 dpi quality (9600 dpi x 600 dpi)
Duplex Print	Yes
Print Memory	384MB (Shared)
Scanner Specification	
Scan Type	Colour CCD
Scan Resolution	600 x 600 dpi (optical)
Colour Depth	24-bit
Document Size	Platen : Up to 8.5" x 14" / 215.9 x 355.6mm ADF: 5.5" x 5" to 8.5" x 14" / 139.7 x 128mm to 215.9 x 355.6mm
Duplex Scan	Yes
Compatibility	TWAIN, WIA (*7)
Output File Format	JPEG, TIFF
PullScan	
Scan To PC	
Send Specification	
Scan to E-Mail	Yes
Internet Fax	Yes
Other Protocol	SMB, FTP
File Format	Hi-compression PDF, PDF, JPEG, TIFF
Scan To Media Specification	
Scan to USB	
File Format	
FAX/PC Specification	
Modem Speed	Up to 33.6 Kbps
Fax Resolution	Up to 406 x 391 dpi
Memory Capacity	Up to 1,000 pages (*3)
One-touch Dial	
Speed Dial	200 location
Duplex Fax	Yes (transmission/reception)
Receive Mode	FAX Only, Manual, Answering, Fax/Tel Auto SW
Fax Features	Remote RX, Delayed TX, Dual Access
Memory Backup	Yes, 1 hour
PC Fax	Yes (sending only)
Interface/Software	
Standard Interface(s)	USB 2.0, 10/100 Base-T Ethernet (Network), USB Memory slot (x2)
USB Function	Print and PC Fax
Network Function	Print, PC Fax, Scan and Send
Network Protocol	TCP/IP
Operating System	Windows® 7, Windows Server® 2008, Windows Vista®, Windows Server® 2003, Windows® XP/2000 Mac® OS X 10.4.9 & up (*4), Linux(*5)
General Specification	
LCD Display	3.5 inch colour TFT
Dimensions (W x D x H)	546mm(W) x 527mm(D) x 632mm(H)
Weight(w/o CRG, w/CRG)	38.5kg (w/o CRG), 43.3kg (w/ CRG)
Power Consumption	Max : 1210W Energy Saver Mode : 1.2W (Stand alone) / 17W (Network connection)
Cartridge Type	Single Cartridge System

For reliability and continued smooth running of your Canon laser – use genuine Canon Toner



Optional Genuine Canon Extended Warranty is available on this product

