V7 MICRO SDHC CLASS 4 + ADAPTER

Store / transport - photos, video and data

The V7 Micro SDHC Class 4 memory card provides a secure way to capture, store or transport your digital photos, videos, or data files. These easily transportable memory cards are perfect for professional or home use. Ranging in capacities of 4GB, 8GB, 16GB and 32GB there's an option for all your needs. The V7 Micro SDHC memory cards come with the full size SD adapter. Backed by a limited 5 year warranty these reliable memory cards provide peace of mind and freedom to transport your most precious data.

Secure, High Capacity Class 4 Micro SDHC Memory Cards









Miggs Mapper

Card

16GB

Migro Adapter

32GB


Ca

Features & Benefits:

- Secure digital high capacity data storage
- High speed data transfer: Read >10MB/s, Write >4MB/s
- Durable impact resistant plastic housing
- Plug and Play –Windows: 2000/XP/Vista/7/8 Mac: OS 9.0+ Linux: Kernel 2.4 operating systems
- Includes adapter for transferring to SD application
- 10 years Data retention 10,000 Program/Erase Cycles
- Write protect switch to lockout data deletion

Full Color Retail Package





3/8"	*
: #	<u>UPC</u>
H4GCL4R-1N	66291903393

<u>V / Part #</u>	<u>UPC</u>
VAMSDH4GCL4R-1N	6629190
VAMSDH8GCL4R-1N	6629190
VAMSDH16GCL4R-1N	6629190
VAMSDH32GCL4R-1N	6629190

-1N 662919033915 -1N 662919033922 R-1N 662919033939 R-1N 662919044423

Specifications					
V7 Part #s:	VAMSDH4GCL4R-1N, VAMSDH8GCL4R-1N, VAMSDH16GCL4R-1N, VAMSDH32GCL4R-1N				
MSRP:	4GB \$13.99, 8GB \$22.99, 16GB \$43.99, 32GB \$51.20				
Compatibility:	All SDHC enabled host devices				
Interface:	Class 4				
Housing	Durable impact resistant platic housing				
Transfer Rate	Read >10MB/s, Write >4MB/s				
Package includes:	Micro SDHC Card + SD adapter card				
Product dim. (L/W/H):	0. 95"x 0.39"x 0.07" / 32 x 24 x 2 mm				
Product weight:	0.003 oz / 1 g				
Packaging dim. (L/W/H):	5.07" x 3.58" x 0.25" / 12.9 x 8.1 x 0.65 cm				
Packaging type:	Retail Full Color Blister with hang tag				
Compliance:	CE, FCC, RoHS				
UPC:	See chart below				
Warranty:	5 Year Limited Warranty				
Country of origin:	Made in Taiwan				

Approx.*	* PHOTO				VIDEO			MUSIC
CAPACITY	6МР	8МР	10MP	12MP	6Mbps HD	9Mbps HD	13Mbps HD	ACC, MP3 HQ 128Kbps
4GB	1,592	1,159	809	677	68 min	45 min	31 min	68 hr 14 min
8GB	3,182	2,318	1,618	1,354	135 min	90 min	63 min	136 hr 27 min
16GB	6,364	4,636	3,236	2,708	271 min	181 min	125 min	272 hr 54 min
32GB	12,728	9,272	6,471	5,416	542 min	362 min	250 min	545 hr 48 min

^{*} All numbers are approximate. Actual storage will depend on size of data and compression used.

PLACING ORDER: For a complete list of V7 products or placing an order, visit www.ingrammicro.com/V7 or contact your Ingram Micro Sales Representative at 800-456-8000.