

SD16

16 Port 10/100Mbps Fast Ethernet Switch

This switch is an unmanaged 10/100Mbps Fast Ethernet Switch that offers solutions to increase Ethernet workgroup bandwidth. It was designed for a network environment where traffic and the number of users increase continuously. The SD16, with its small desktop size, was specifically designed for small to middle workgroups requiring immediate access to a rapidly growing network through a wide range of user-reliable functions.



Specifications

Header

- Manufacturer:
 - Amer
- Model:
 - SD16

Performance

- Switching Capacity:
 - 3.2 Gbps
- MAC Address Table Size:
 - 8k
- Networking Standards:
 - IEEE 802.3; IEEE 802.3u;
 - IEEE 802.3x;

Ports & Port Features

- RJ45 10/100Base-T:
 - 16
- Auto-negotiation:
 - For port speed and duplex mode
- LED Status Indicators:
 - Port link activity; Port connectivity;
 - Power;

Warranty and Support

- Warranty: Limited lifetime Warranty for as long as the original customer/end user owns the product, or 5 years after product discontinuance, whichever occurs first (excluding power supplies and fans); Power supplies and fans carry a limited 1 year warranty.
- Support: Free technical support (phone/email); Software support; Premium incident support.

Electronic Features & Electrical Emissions

- Emissions:
 - FCC Class A; CE Mark Class A; VCCI-A
- Power Supply:
 - External power adapter 7.5VDC/1A

Environmental Parameters

- Humidity Range Operating:
 - 10-90%
- Max Operating Temperature:
 - 104F
- Min Operating Temperature:
 - 32F

Dimensions & Weight

- Width x Depth x Height:
 - 7.2" x 4.9" x 1.7"
 - 18.4 x 4.4 x 12.4 cm
- Weight:
 - 2.50lbs(1.13kg)