



PD4CB

Overview

PD4CB power distribution modules convert a single AC or DC input into four (4) individual outputs.

Specifications

Input:

- 12VDC or 24VDC up to 10 amp, (total output current should not exceed max current rating of power supply employed).

Output:

- Four (4) PTC protected outputs.
- PTCs are rated @ 2.5 amp.
- Surge suppression.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- 61.42 or 122.84 BTU/Hr.

Features:

- Power LED indicator.

Mechanical:

- Snap track mountable (order part # ST3).
- Product weight (approx.): 0.15 lbs. (0.07 kg).
- Shipping weight (approx.): 0.25 lbs. (0.11kg).

Board Dimensions (W x L x D approximate)

3.25" x 5.25" x 1" (82.55mm x 133.35mm x 25.4mm)

Mounting Diagram

